

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1286972

Luminaire Tested: P3AS09R609030D2WDE010 E3DLP1WMH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1286972
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-37)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS09R609030D2WDE010 E3DLP1WMH
Description: 3in Adjustable Dim to Warm LED luminaire with, R60 optic, 3000K CCT AND, 90CRI ,
E3DLP1WMH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 487.0 lumens
Efficiency: N/A
Efficacy: 33.1 lumens/watt
Spacing Criteria (0/90/45): 0.79 / 0.79 / 0.83
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 14.7
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1286972

CATALOG NUMBER: P3AS09R609030D2WDE010 E3DLP1WMH

Luminous Intensity Polar Plot



TEST NUMBER: P1286972

CATALOG NUMBER: P3AS09R609030D2WDE010 E3DLP1WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	107	105	110	108	105	103	104	102	100		100	98	97		96
2	107	101	97	93	104	100	96	92	96	93	90		93	91	88		91
3	101	94	88	84	99	92	87	83	90	86	82		87	84	81		85
4	95	87	81	77	93	86	80	76	84	79	75		82	78	74		80
5	90	81	75	70	88	80	74	70	78	73	69		77	72	69		75
6	85	76	69	65	84	75	69	65	73	68	64		72	67	64		71
7	81	71	65	60	79	70	64	60	69	64	60		68	63	59		67
8	77	67	60	56	75	66	60	56	65	60	56		64	59	55		63
9	73	63	57	52	72	62	56	52	61	56	52		60	55	52		60
10	69	59	53	49	68	59	53	49	58	53	49		57	52	49		56

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	123411
5°	120647
10°	112957
15°	101340
20°	87134
25°	72053
30°	56945
35°	42269
40°	29112
45°	18265
50°	10030
55°	5887
60°	5263
65°	4514
70°	3847
75°	3982
80°	3410
85°	3271

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 18265 cd/sqm

TEST NUMBER: P1286972

CATALOG NUMBER: P3AS09R609030D2WDE010 E3DLP1WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	51.0	10.5
10°-20°	124.0	25.5
20°-30°	136.0	27.9
30°-40°	99.1	20.3
40°-50°	46.8	9.6
50°-60°	15.3	3.1
60°-70°	8.7	1.8
70°-80°	4.7	1.0
80°-90°	1.5	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	311.0	63.9
0°-40°	410.0	84.2
0°-60°	472.1	97.0
0°-90°	487.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	487.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	563	
5°	548	51
15°	446	124
25°	298	136
35°	158	99
45°	59	47
55°	15	15
65°	9	9
75°	5	5
85°	1	1
90°	0	

TEST NUMBER: P1286972

CATALOG NUMBER: P3AS09R609030D2WDE010 E3DLP1WMH

CANDELA DISTRIBUTION (FULL):

	0°
0°	562.8
2.5°	559.5
5°	548.1
7.5°	530.7
10°	507.3
12.5°	479.2
15°	446.4
17.5°	410.9
20°	373.4
22.5°	335.3
25°	297.8
27.5°	260.3
30°	224.9
32.5°	190.7
35°	157.9
37.5°	128.5
40°	101.7
42.5°	78.3
45°	58.9
47.5°	42.8
50°	29.4
52.5°	19.4
55°	15.4
57.5°	13.4
60°	12.0
62.5°	10.0
65°	8.7
67.5°	7.4
70°	6.0
72.5°	5.4
75°	4.7
77.5°	3.3
80°	2.7
82.5°	2.0
85°	1.3
87.5°	0.7
90°	0.0

(END OF REPORT)