

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1286982

Luminaire Tested: P3AS09R659030D2WDE010 E3D1WH

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1286982
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2501-338-16)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS09R659030D2WDE010 E3D1WH
Description: 3in Adjustable Dim to Warm LED luminaire with, R65 optic, 3000K CCT AND, 90CRI , E3D1WH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 798.0 lumens
Efficiency: N/A
Efficacy: 54.3 lumens/watt
Spacing Criteria (0/90/45): 0.92 / 0.92 / 0.88
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 14.7
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1286982
CATALOG NUMBER: P3AS09R659030D2WDE010 E3D1WH

Luminous Intensity Polar Plot





TEST NUMBER: P1286982
 CATALOG NUMBER: P3AS09R659030D2WDE010 E3D1WH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	114	111	109	106	111	109	107	105	105	103	102	101	100	99	98	97	96	94			94
2	108	104	100	96	106	102	98	95	99	96	93	96	93	91	93	91	89	88			88
3	103	97	92	88	101	95	91	88	93	89	86	90	87	85	88	86	83	82			82
4	98	91	85	81	96	90	85	81	87	83	80	85	82	79	84	81	78	77			77
5	93	85	79	75	92	84	79	75	82	78	74	81	77	74	79	76	73	72			72
6	89	80	74	70	87	79	74	70	78	73	69	76	72	69	75	71	68	67			67
7	84	75	70	65	83	75	69	65	73	69	65	72	68	65	71	67	64	63			63
8	80	71	65	61	79	71	65	61	69	64	61	68	64	61	67	63	60	59			59
9	77	67	61	58	76	67	61	57	66	61	57	65	60	57	64	60	57	56			56
10	73	64	58	54	72	63	58	54	62	57	54	62	57	54	61	57	54	52			52

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	213821
5°	198547
10°	192003
15°	185041
20°	171072
25°	155864
30°	120424
35°	69814
40°	27709
45°	11784
50°	2797
55°	382
60°	307
65°	156
70°	192
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 11784 cd/sqm



TEST NUMBER: P1286982

CATALOG NUMBER: P3AS09R659030D2WDE010 E3D1WH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	85.1	10.7
10°-20°	227.1	28.5
20°-30°	287.4	36.0
30°-40°	163.7	20.5
40°-50°	32.5	4.1
50°-60°	1.7	0.2
60°-70°	0.4	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	599.6	75.1
0°-40°	763.3	95.7
0°-60°	797.5	99.9
0°-90°	798.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	798.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	975	
5°	902	85
15°	815	227
25°	644	287
35°	261	164
45°	38	33
55°	1	2
65°	0	0
75°	0	0
85°	0	0
90°	0	

TEST NUMBER: P1286982

CATALOG NUMBER: P3AS09R659030D2WDE010 E3D1WH

CANDELA DISTRIBUTION (FULL):

	0°
0°	975.1
1°	967.9
2°	952.2
3°	933.8
4°	915.8
5°	902.0
6°	891.8
7°	883.6
8°	876.4
9°	869.2
10°	862.3
11°	854.8
12°	846.9
13°	837.4
14°	827.2
15°	815.1
16°	800.6
17°	784.9
18°	767.8
19°	749.8
20°	733.1
21°	716.0
22°	700.6
23°	684.5
24°	665.8
25°	644.2
26°	618.3
27°	587.1
28°	552.0
29°	514.6
30°	475.6
31°	432.6
32°	390.0
32.5°	368.0
33°	346.7
34°	303.4
35°	260.8
36°	221.4
37°	182.4
37.5°	162.4
38°	146.3
39°	118.4
40°	96.8
42.5°	59.7
45°	38.0



TEST NUMBER: P1286982
CATALOG NUMBER: P3AS09R659030D2WDE010 E3D1WH

CANDELA DISTRIBUTION (continued):

	0°
47.5°	22.3
50°	8.2
52.5°	1.6
55°	1.0
57.5°	0.7
60°	0.7
62.5°	0.7
65°	0.3
67.5°	0.3
70°	0.3
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)