

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1287855

Luminaire Tested: P3AS05R15W2N902750DE010 E3DLP1WH_4000K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1287855
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-3)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS05R15W2N902750DE010 E3DLP1WH_4000K
Description: 3in Adjustable Tunable White LED luminaire with, R15 optic, 4000K CCT AND, 90CRI ,
E3DLP1WH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 416.9 lumens
Efficiency: N/A
Efficacy: 70.7 lumens/watt
Spacing Criteria (0/90/45): 0.4 / 0.4 / 0.43
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 5.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1287855

CATALOG NUMBER: P3AS05R15W2N902750DE010 E3DLP1WH_4000K

Luminous Intensity Polar Plot



TEST NUMBER: P1287855

CATALOG NUMBER: P3AS05R15W2N902750DE010 E3DLP1WH_4000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20				20				20
RC	80				70				50				30				10				0				0				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																													
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	99	98	97	95	91	87	83	80	77	74	72
1	114	112	110	108	112	110	108	106	106	104	103	102	101	100	99	98	97	95	91	87	83	80	77	74	72	69	67	65	63
2	110	106	103	100	108	104	101	99	101	99	97	98	96	95	96	94	93	91	87	83	80	77	74	72	69	67	65	63	61
3	106	101	97	93	104	99	96	93	97	94	91	94	92	90	92	90	88	87	83	79	76	73	70	67	65	63	61	59	57
4	102	96	92	88	100	95	91	88	93	89	87	91	88	86	89	87	85	83	79	76	73	70	67	65	63	61	59	57	55
5	98	92	87	84	97	91	87	83	89	86	83	88	84	82	86	83	81	80	76	73	70	67	65	63	61	59	57	55	53
6	95	88	83	80	94	87	83	80	86	82	79	85	81	79	83	80	78	77	73	70	67	65	63	61	59	57	55	53	51
7	92	85	80	77	91	84	80	76	83	79	76	82	78	76	81	78	75	74	70	67	65	63	61	59	57	55	53	51	49
8	89	81	77	74	88	81	77	73	80	76	73	79	76	73	78	75	73	72	68	65	63	61	59	57	55	53	51	49	47
9	86	79	74	71	85	78	74	71	77	73	71	77	73	70	76	73	70	69	65	63	61	59	57	55	53	51	49	47	45
10	84	76	71	68	83	76	71	68	75	71	68	74	71	68	74	70	68	67	63	61	59	57	55	53	51	49	47	45	43

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	356221
5°	316200
10°	219591
15°	129853
20°	73973
25°	42269
30°	23396
35°	12474
40°	6899
45°	3752
50°	2320
55°	1835
60°	1579
65°	1453
70°	1282
75°	1356
80°	1010
85°	1006

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 3752 cd/sqm

TEST NUMBER: P1287855

CATALOG NUMBER: P3AS05R15W2N902750DE010 E3DLP1WH_4000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	122.2	29.3
10°-20°	161.2	38.7
20°-30°	83.0	19.9
30°-40°	31.2	7.5
40°-50°	10.2	2.4
50°-60°	4.4	1.0
60°-70°	2.8	0.7
70°-80°	1.6	0.4
80°-90°	0.4	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	366.4	87.9
0°-40°	397.5	95.3
0°-60°	412.1	98.8
0°-90°	416.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	416.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1624	
5°	1436	122
15°	572	161
25°	175	83
35°	47	31
45°	12	10
55°	5	4
65°	3	3
75°	2	2
85°	0	0
90°	0	

TEST NUMBER: P1287855

CATALOG NUMBER: P3AS05R15W2N902750DE010 E3DLP1WH_4000K

CANDELA DISTRIBUTION (FULL):

0°	
0°	1624.5
1°	1621.3
2°	1600.0
3°	1559.4
4°	1506.0
5°	1436.5
6°	1357.8
7°	1271.4
8°	1175.4
9°	1080.6
10°	986.2
12.5°	758.8
15°	572.0
17.5°	428.2
20°	317.0
22.5°	236.6
25°	174.7
27.5°	127.3
30°	92.4
32.5°	65.5
35°	46.6
37.5°	33.3
40°	24.1
42.5°	17.3
45°	12.1
47.5°	8.8
50°	6.8
52.5°	5.6
55°	4.8
57.5°	4.0
60°	3.6
62.5°	3.2
65°	2.8
67.5°	2.4
70°	2.0
72.5°	2.0
75°	1.6
77.5°	1.2
80°	0.8
82.5°	0.8
85°	0.4
87.5°	0.0
90°	0.0

(END OF REPORT)