

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1287000

Luminaire Tested: P3AS09R659030D2WDE010 E3DLP1WH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1287000
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-43)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS09R659030D2WDE010 E3DLP1WH
Description: 3in Adjustable Dim to Warm LED luminaire with, R65 optic, 3000K CCT AND, 90CRI ,
E3DLP1WH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 671.0 lumens
Efficiency: N/A
Efficacy: 45.6 lumens/watt
Spacing Criteria (0/90/45): 0.88 / 0.88 / 0.88
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 14.7
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1287000
CATALOG NUMBER: P3AS09R659030D2WDE010 E3DLP1WH

Luminous Intensity Polar Plot





TEST NUMBER: P1287000
 CATALOG NUMBER: P3AS09R659030D2WDE010 E3DLP1WH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	113	110	107	105	111	108	106	103	104	102	100	100	99	97	97	96	94	93				93
2	107	102	98	94	105	100	96	93	97	94	91	94	91	89	91	89	87	85				85
3	101	95	89	85	99	93	88	84	90	86	83	88	85	82	86	83	80	79				79
4	96	88	82	78	94	87	81	77	85	80	76	83	79	75	81	77	74	73				73
5	91	82	76	71	89	81	75	71	79	74	70	77	73	70	76	72	69	68				68
6	86	77	70	66	84	76	70	66	74	69	65	73	68	65	72	67	64	63				63
7	82	72	66	61	80	71	65	61	70	64	61	69	64	60	67	63	60	58				58
8	77	67	61	57	76	67	61	57	66	60	57	65	60	56	64	59	56	55				55
9	74	64	57	53	72	63	57	53	62	57	53	61	56	53	60	56	53	51				51
10	70	60	54	50	69	59	54	50	59	53	50	58	53	50	57	53	49	48				48

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	158233
5°	156350
10°	150409
15°	140886
20°	126734
25°	107619
30°	84165
35°	59963
40°	39245
45°	24251
50°	12315
55°	4358
60°	3815
65°	3840
70°	3462
75°	3389
80°	3410
85°	3271

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 24251 cd/sqm



TEST NUMBER: P1287000

CATALOG NUMBER: P3AS09R659030D2WDE010 E3DLP1WH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	66.7	9.9
10°-20°	172.7	25.7
20°-30°	201.9	30.1
30°-40°	141.1	21.0
40°-50°	62.1	9.3
50°-60°	13.8	2.1
60°-70°	7.0	1.0
70°-80°	4.2	0.6
80°-90°	1.5	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	441.3	65.8
0°-40°	582.4	86.8
0°-60°	658.3	98.1
0°-90°	671.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	671.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	722	
5°	710	67
15°	621	173
25°	445	202
35°	224	141
45°	78	62
55°	11	14
65°	7	7
75°	4	4
85°	1	1
90°	0	



TEST NUMBER: P1287000
CATALOG NUMBER: P3AS09R659030D2WDE010 E3DLP1WH

CANDELA DISTRIBUTION (FULL):

	0°
0°	721.6
2.5°	719.0
5°	710.3
7.5°	695.6
10°	675.5
12.5°	650.7
15°	620.6
17.5°	583.9
20°	543.1
22.5°	496.9
25°	444.8
27.5°	389.9
30°	332.4
32.5°	276.9
35°	224.0
37.5°	177.9
40°	137.1
42.5°	103.7
45°	78.2
47.5°	57.5
50°	36.1
52.5°	18.7
55°	11.4
57.5°	10.0
60°	8.7
62.5°	8.0
65°	7.4
67.5°	6.0
70°	5.4
72.5°	4.7
75°	4.0
77.5°	3.3
80°	2.7
82.5°	2.0
85°	1.3
87.5°	0.7
90°	0.0

(END OF REPORT)