

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1287019

Luminaire Tested: P3AS09R709030D2WDE010 E3DLP1GPH

Issue Date: 1/30/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1287019  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-45)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS09R709030D2WDE010 E3DLP1GPH  
Description: 3in Adjustable Dim to Warm LED luminaire with, R70 optic, 3000K CCT AND, 90CRI ,  
E3DLP1GPH TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 236.0 lumens  
Efficiency: N/A  
Efficacy: 16.1 lumens/watt  
Spacing Criteria (0/90/45): 0.82 / 0.82 / 0.87  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 14.7  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1287019  
CATALOG NUMBER: P3AS09R709030D2WDE010 E3DLP1GPH

### Luminous Intensity Polar Plot





TEST NUMBER: P1287019

CATALOG NUMBER: P3AS09R709030D2WDE010 E3DLP1GPH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	113	110	107	104	110	107	105	103	103	101	100	100	98	97	96	95	94	92				92
2	106	101	97	93	104	99	95	92	96	93	90	93	90	88	90	88	86	84				84
3	100	93	88	83	98	92	87	83	89	85	81	87	83	80	84	81	79	77				77
4	95	86	80	76	93	85	80	75	83	78	74	81	77	73	79	76	73	71				71
5	89	80	74	69	88	79	73	69	78	72	68	76	71	68	74	70	67	65				65
6	85	75	68	64	83	74	68	64	73	67	63	71	66	63	70	65	62	61				61
7	80	70	64	59	79	69	63	59	68	62	58	67	62	58	66	61	58	56				56
8	76	66	59	55	75	65	59	55	64	58	54	63	58	54	62	57	54	52				52
9	72	62	55	51	71	61	55	51	60	55	51	59	54	51	58	54	50	49				49
10	69	58	52	48	67	58	52	48	57	51	48	56	51	48	55	51	47	46				46

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	55346
5°	54347
10°	51235
15°	46493
20°	40674
25°	34308
30°	28106
35°	21790
40°	15601
45°	9861
50°	4912
55°	3020
60°	2588
65°	2387
70°	2116
75°	1949
80°	1642
85°	1761

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 9861 cd/sqm



TEST NUMBER: P1287019

CATALOG NUMBER: P3AS09R709030D2WDE010 E3DLP1GPH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	23.0	9.8
10°-20°	57.0	24.2
20°-30°	64.9	27.5
30°-40°	50.8	21.5
40°-50°	24.9	10.6
50°-60°	7.7	3.2
60°-70°	4.5	1.9
70°-80°	2.4	1.0
80°-90°	0.7	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	145.0	61.4
0°-40°	195.7	82.9
0°-60°	228.3	96.7
0°-90°	236.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	236.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	252	
5°	247	23
15°	205	57
25°	142	65
35°	81	51
45°	32	25
55°	8	8
65°	5	5
75°	2	2
85°	1	1
90°	0	



TEST NUMBER: P1287019

CATALOG NUMBER: P3AS09R709030D2WDE010 E3DLP1GPH

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	252.4
2.5°	251.1
5°	246.9
7.5°	240.0
10°	230.1
12.5°	218.6
15°	204.8
17.5°	190.1
20°	174.3
22.5°	157.9
25°	141.8
27.5°	126.1
30°	111.0
32.5°	95.9
35°	81.4
37.5°	67.6
40°	54.5
42.5°	42.3
45°	31.8
47.5°	22.3
50°	14.4
52.5°	9.5
55°	7.9
57.5°	6.9
60°	5.9
62.5°	5.3
65°	4.6
67.5°	3.9
70°	3.3
72.5°	2.6
75°	2.3
77.5°	2.0
80°	1.3
82.5°	1.0
85°	0.7
87.5°	0.3
90°	0.0

(END OF REPORT)