

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1287021

Luminaire Tested: P3AS09R709030D2WDE010 E3DLP1LI

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1287021
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-45)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS09R709030D2WDE010 E3DLP1LI
Description: 3in Adjustable Dim to Warm LED luminaire with, R70 optic, 3000K CCT AND, 90CRI ,
E3DLP1LI TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 481.0 lumens
Efficiency: N/A
Efficacy: 32.7 lumens/watt
Spacing Criteria (0/90/45): 0.82 / 0.82 / 0.87
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 14.7
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1287021
CATALOG NUMBER: P3AS09R709030D2WDE010 E3DLP1LI

Luminous Intensity Polar Plot





TEST NUMBER: P1287021
 CATALOG NUMBER: P3AS09R709030D2WDE010 E3DLP1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	113	110	107	104	110	107	105	103	103	101	100	100	98	97	96	95	94	92				92
2	106	101	97	93	104	99	95	92	96	93	90	93	90	88	90	88	86	84				84
3	100	93	88	83	98	92	87	83	89	85	81	87	83	80	84	81	79	77				77
4	95	86	80	76	93	85	80	75	83	78	74	81	77	73	79	76	73	71				71
5	89	80	74	69	88	79	73	69	78	72	68	76	71	68	74	70	67	65				65
6	85	75	68	64	83	74	68	64	73	67	63	71	66	63	70	65	62	61				61
7	80	70	64	59	79	69	63	59	68	62	58	67	62	58	66	61	58	56				56
8	76	66	59	55	75	65	59	55	64	58	54	63	58	54	62	57	54	52				52
9	72	62	55	51	71	61	55	51	60	55	51	59	54	51	58	54	50	49				49
10	69	58	52	48	67	58	52	48	57	51	48	56	51	48	55	51	47	46				46

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	112820
5°	110742
10°	104429
15°	94779
20°	82911
25°	69923
30°	57249
35°	44410
40°	31802
45°	20126
50°	10030
55°	6155
60°	5263
65°	4877
70°	4296
75°	3982
80°	3410
85°	3271

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 20126 cd/sqm



TEST NUMBER: P1287021

CATALOG NUMBER: P3AS09R709030D2WDE010 E3DLP1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	47.0	9.8
10°-20°	116.2	24.2
20°-30°	132.3	27.5
30°-40°	103.5	21.5
40°-50°	50.8	10.6
50°-60°	15.6	3.3
60°-70°	9.3	1.9
70°-80°	5.0	1.0
80°-90°	1.5	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	295.4	61.4
0°-40°	398.9	82.9
0°-60°	465.3	96.7
0°-90°	481.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	481.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	514	
5°	503	47
15°	418	116
25°	289	132
35°	166	103
45°	65	51
55°	16	16
65°	9	9
75°	5	5
85°	1	1
90°	0	



TEST NUMBER: P1287021
CATALOG NUMBER: P3AS09R709030D2WDE010 E3DLP1LI

CANDELA DISTRIBUTION (FULL):

0°	
0°	514.5
2.5°	511.8
5°	503.1
7.5°	489.1
10°	469.0
12.5°	445.6
15°	417.5
17.5°	387.4
20°	355.3
22.5°	321.8
25°	289.0
27.5°	256.9
30°	226.1
32.5°	195.4
35°	165.9
37.5°	137.8
40°	111.1
42.5°	86.3
45°	64.9
47.5°	45.5
50°	29.4
52.5°	19.4
55°	16.1
57.5°	14.1
60°	12.0
62.5°	10.7
65°	9.4
67.5°	8.0
70°	6.7
72.5°	5.4
75°	4.7
77.5°	4.0
80°	2.7
82.5°	2.0
85°	1.3
87.5°	0.7
90°	0.0

(END OF REPORT)