

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1287905

Luminaire Tested: P3AS05R15W2N902765DE010 E3CD1MMS_5000K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1287905
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-4)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS05R15W2N902765DE010 E3CD1MMS_5000K
Description: 3in Adjustable Tunable White LED luminaire with, R15 optic, 5000K CCT AND, 90CRI ,
E3CD1MMS TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 505.0 lumens
Efficiency: N/A
Efficacy: 85.6 lumens/watt
Spacing Criteria (0/90/45): 0.3 / 0.3 / 0.29
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 5.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1287905

CATALOG NUMBER: P3AS05R15W2N902765DE010 E3CD1MMS_5000K

Luminous Intensity Polar Plot



TEST NUMBER: P1287905

CATALOG NUMBER: P3AS05R15W2N902765DE010 E3CD1MMS_5000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10		0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102		100
1	116	114	112	111	113	112	110	109	108	107	106		104	103	103		101	100	100		98
2	113	110	107	105	111	108	106	104	105	103	101		102	101	99		99	98	97		96
3	110	106	103	100	108	105	102	100	102	100	98		100	98	97		98	97	95		94
4	107	103	100	97	106	102	99	97	100	97	95		98	96	94		97	95	93		92
5	105	100	97	94	104	99	96	94	98	95	93		96	94	92		95	93	92		91
6	103	98	94	92	102	97	94	92	96	93	91		95	92	91		94	92	90		89
7	101	96	92	90	100	95	92	90	94	91	89		93	91	89		92	90	89		88
8	99	94	90	88	98	93	90	88	92	90	88		92	89	87		91	89	87		86
9	97	92	89	87	97	92	89	86	91	88	86		90	88	86		90	87	86		85
10	96	90	87	85	95	90	87	85	89	87	85		89	86	85		88	86	85		84

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	981610
5°	822670
10°	387523
15°	116822
20°	43240
25°	16815
30°	6279
35°	1927
40°	687
45°	372
50°	273
55°	306
60°	351
65°	208
70°	256
75°	339
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 372 cd/sqm

TEST NUMBER: P1287905

CATALOG NUMBER: P3AS05R15W2N902765DE010 E3CD1MMS_5000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	288.9	57.2
10°-20°	171.7	34.0
20°-30°	36.1	7.1
30°-40°	5.8	1.2
40°-50°	1.0	0.2
50°-60°	0.7	0.1
60°-70°	0.4	0.1
70°-80°	0.3	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	496.8	98.4
0°-40°	502.6	99.5
0°-60°	504.3	99.9
0°-90°	505.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	505.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	4476	
5°	3737	289
15°	515	172
25°	70	36
35°	7	6
45°	1	1
55°	1	1
65°	0	0
75°	0	0
85°	0	0
90°	0	

TEST NUMBER: P1287905

CATALOG NUMBER: P3AS05R15W2N902765DE010 E3CD1MMS_5000K

CANDELA DISTRIBUTION (FULL):

0°	
0°	4476.5
1°	4462.5
2°	4391.4
3°	4249.3
4°	4040.9
5°	3737.4
6°	3380.9
7°	2973.3
8°	2584.0
9°	2143.2
10°	1740.4
12.5°	939.0
15°	514.6
17.5°	301.4
20°	185.3
22.5°	113.4
25°	69.5
27.5°	41.9
30°	24.8
32.5°	14.0
35°	7.2
37.5°	4.0
40°	2.4
42.5°	1.6
45°	1.2
47.5°	0.8
50°	0.8
52.5°	0.8
55°	0.8
57.5°	0.8
60°	0.8
62.5°	0.4
65°	0.4
67.5°	0.4
70°	0.4
72.5°	0.4
75°	0.4
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)