

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1287094

Luminaire Tested: P3AS13R259030D2WDE010 E3D1WH

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1287094
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2501-338-9)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R259030D2WDE010 E3D1WH
Description: 3in Adjustable Dim to Warm LED luminaire with, R25 optic, 3000K CCT AND, 90CRI , E3D1WH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1455.0 lumens
Efficiency: N/A
Efficacy: 72.4 lumens/watt
Spacing Criteria (0/90/45): 0.44 / 0.44 / 0.4
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 20.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1287094
CATALOG NUMBER: P3AS13R259030D2WDE010 E3D1WH

Luminous Intensity Polar Plot





TEST NUMBER: P1287094

CATALOG NUMBER: P3AS13R259030D2WDE010 E3D1WH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	589.5	40.5
10°-20°	670.4	46.1
20°-30°	155.8	10.7
30°-40°	32.7	2.2
40°-50°	5.3	0.4
50°-60°	0.9	0.1
60°-70°	0.4	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1415.7	97.3
0°-40°	1448.4	99.5
0°-60°	1454.6	100.0
0°-90°	1455.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1455.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	7267	
5°	6706	589
15°	2403	670
25°	313	156
35°	48	33
45°	6	5
55°	1	1
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P1287094
CATALOG NUMBER: P3AS13R259030D2WDE010 E3D1WH

CANDELA DISTRIBUTION (FULL):

0°	
0°	7266.9
1°	7252.2
2°	7176.7
3°	7070.7
4°	6908.7
5°	6706.1
6°	6446.1
7°	6173.9
8°	5868.4
9°	5523.9
10°	5129.3
11°	4671.9
12°	4147.0
13°	3572.0
14°	2970.6
15°	2403.0
16°	1900.7
17°	1480.8
18°	1164.8
19°	931.6
20°	770.7
21°	644.1
22°	540.7
23°	451.6
24°	377.7
25°	313.4
27.5°	185.7
30°	116.1
32.5°	74.4
35°	47.5
37.5°	28.5
40°	14.8
42.5°	9.5
45°	6.3
47.5°	3.7
50°	2.1
52.5°	1.1
55°	1.1
57.5°	0.5
60°	0.5
62.5°	0.5
65°	0.5
67.5°	0.5
70°	0.0
72.5°	0.0



TEST NUMBER: P1287094
CATALOG NUMBER: P3AS13R259030D2WDE010 E3D1WH

CANDELA DISTRIBUTION (continued):

	0°
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)