

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1288135

Luminaire Tested: P3AS05R20W2N902750DE010 E3DL1LI_3000K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1288135
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-7)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS05R20W2N902750DE010 E3DL1LI_3000K
Description: 3in Adjustable Tunable White LED luminaire with, R20 optic, 3000K CCT AND, 90CRI ,
E3DL1LI TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 409.1 lumens
Efficiency: N/A
Efficacy: 69.3 lumens/watt
Spacing Criteria (0/90/45): 0.44 / 0.44 / 0.46
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 5.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1288135

CATALOG NUMBER: P3AS05R20W2N902750DE010 E3DL1LI_3000K

Luminous Intensity Polar Plot



TEST NUMBER: P1288135

CATALOG NUMBER: P3AS05R20W2N902750DE010 E3DL1LI_3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20				20				20
RC	80				70				50				30				10				0				0				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																													
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	102	102	102	102	102	102	102	102	102	102	102	100
1	114	112	110	108	112	110	108	106	106	104	103	102	101	100	99	98	97	97	98	97	99	98	97	99	98	97	99	98	95
2	110	106	102	100	108	104	101	98	101	98	96	98	96	94	95	94	92	95	94	92	95	94	92	95	94	92	95	94	91
3	106	100	96	93	104	99	95	92	97	93	91	94	92	89	92	90	88	92	90	88	92	90	88	92	90	88	92	90	87
4	102	96	91	88	100	95	90	87	92	89	86	91	88	85	89	86	84	89	86	84	89	86	84	89	86	84	89	86	83
5	98	91	87	83	97	90	86	83	89	85	82	87	84	81	86	83	81	86	83	81	86	83	81	86	83	81	86	83	79
6	95	87	83	79	93	87	82	79	85	81	78	84	81	78	83	80	77	83	80	77	83	80	77	83	80	77	83	80	76
7	91	84	79	76	90	83	79	76	82	78	75	81	78	75	80	77	75	80	77	75	80	77	75	80	77	75	80	77	73
8	88	81	76	73	87	80	76	73	79	75	72	78	75	72	77	74	72	77	74	72	77	74	72	77	74	72	77	74	71
9	85	78	73	70	85	77	73	70	77	73	70	76	72	69	75	72	69	75	72	69	75	72	69	75	72	69	75	72	68
10	83	75	71	68	82	75	70	67	74	70	67	73	70	67	73	69	67	73	69	67	73	69	67	73	69	67	73	69	66

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	314690
5°	286044
10°	211419
15°	130784
20°	74673
25°	42631
30°	23902
35°	13010
40°	7128
45°	3907
50°	2286
55°	1644
60°	1579
65°	1453
70°	1282
75°	1356
80°	1010
85°	1006

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 3907 cd/sqm

TEST NUMBER: P1288135

CATALOG NUMBER: P3AS05R20W2N902750DE010 E3DL1LI_3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	112.5	27.5
10°-20°	160.7	39.3
20°-30°	83.8	20.5
30°-40°	32.4	7.9
40°-50°	10.5	2.6
50°-60°	4.1	1.0
60°-70°	2.8	0.7
70°-80°	1.6	0.4
80°-90°	0.5	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	357.0	87.3
0°-40°	389.5	95.2
0°-60°	404.1	98.8
0°-90°	409.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	409.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1435	
5°	1300	113
15°	576	161
25°	176	84
35°	49	32
45°	13	11
55°	4	4
65°	3	3
75°	2	2
85°	0	1
90°	0	

TEST NUMBER: P1288135

CATALOG NUMBER: P3AS05R20W2N902750DE010 E3DL1LI_3000K

CANDELA DISTRIBUTION (FULL):

0°	
0°	1435.1
1°	1432.3
2°	1415.3
3°	1389.2
4°	1348.9
5°	1299.5
6°	1241.1
7°	1176.3
8°	1101.2
9°	1028.1
10°	949.5
12.5°	754.7
15°	576.1
17.5°	431.1
20°	320.0
22.5°	237.1
25°	176.2
27.5°	130.0
30°	94.4
32.5°	68.4
35°	48.6
37.5°	35.2
40°	24.9
42.5°	17.8
45°	12.6
47.5°	9.1
50°	6.7
52.5°	5.1
55°	4.3
57.5°	4.0
60°	3.6
62.5°	3.2
65°	2.8
67.5°	2.4
70°	2.0
72.5°	2.0
75°	1.6
77.5°	1.2
80°	0.8
82.5°	0.8
85°	0.4
87.5°	0.4
90°	0.0

(END OF REPORT)