

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1287107

Luminaire Tested: P3AS13R259030D2WDE010 E3DLD1WMH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1287107
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-10)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R259030D2WDE010 E3DLD1WMH
Description: 3in Adjustable Dim to Warm LED luminaire with, R25 optic, 3000K CCT AND, 90CRI ,
E3DLD1WMH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 864.0 lumens
Efficiency: N/A
Efficacy: 43.0 lumens/watt
Spacing Criteria (0/90/45): 0.78 / 0.78 / 0.85
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 20.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1287107

CATALOG NUMBER: P3AS13R259030D2WDE010 E3DLD1WMH

Luminous Intensity Polar Plot



TEST NUMBER: P1287107

CATALOG NUMBER: P3AS13R259030D2WDE010 E3DLD1WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	112	109	106	104	110	107	105	102	103	101	99	99	98	96	96	94	93	91		
2	106	100	96	92	104	99	94	91	95	92	89	92	89	87	89	87	85	83		
3	100	92	87	82	98	91	86	82	88	84	80	86	82	79	83	80	78	76		
4	94	85	79	74	92	84	78	74	82	77	73	80	76	72	78	74	71	70		
5	89	79	73	68	87	78	72	68	76	71	67	75	70	66	73	69	66	64		
6	84	74	67	62	82	73	67	62	71	66	62	70	65	61	69	64	61	59		
7	79	69	62	58	78	68	62	58	67	61	57	66	61	57	65	60	57	55		
8	75	65	58	54	74	64	58	53	63	57	53	62	57	53	61	56	53	51		
9	71	61	54	50	70	60	54	50	59	54	50	58	53	50	57	53	49	48		
10	68	57	51	47	67	57	51	47	56	50	47	55	50	46	54	50	46	45		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	205334
5°	200440
10°	185746
15°	165427
20°	142159
25°	120830
30°	99484
35°	77497
40°	55762
45°	35384
50°	20946
55°	14413
60°	13201
65°	12297
70°	11028
75°	9997
80°	9471
85°	8051

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 35384 cd/sqm

TEST NUMBER: P1287107

CATALOG NUMBER: P3AS13R259030D2WDE010 E3DLD1WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	84.5	9.8
10°-20°	202.3	23.4
20°-30°	228.6	26.5
30°-40°	180.8	20.9
40°-50°	91.3	10.6
50°-60°	36.6	4.2
60°-70°	23.4	2.7
70°-80°	12.9	1.5
80°-90°	3.7	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	515.3	59.6
0°-40°	696.1	80.6
0°-60°	824.0	95.4
0°-90°	864.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	864.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	936	
5°	911	84
15°	729	202
25°	499	229
35°	290	181
45°	114	91
55°	38	37
65°	24	23
75°	12	13
85°	3	4
90°	0	

TEST NUMBER: P1287107

CATALOG NUMBER: P3AS13R259030D2WDE010 E3DLD1WMH

CANDELA DISTRIBUTION (FULL):

0°	
0°	936.4
1°	936.4
2°	933.2
3°	927.8
4°	920.3
5°	910.6
6°	898.8
7°	884.8
8°	869.7
9°	852.5
10°	834.2
11°	813.7
12°	794.4
13°	771.8
14°	750.2
15°	728.7
17.5°	668.4
20°	609.2
22.5°	553.3
25°	499.4
27.5°	446.7
30°	392.9
32.5°	342.3
35°	289.5
37.5°	241.1
40°	194.8
42.5°	151.8
45°	114.1
47.5°	85.0
50°	61.4
52.5°	46.3
55°	37.7
57.5°	34.4
60°	30.1
62.5°	26.9
65°	23.7
67.5°	20.5
70°	17.2
72.5°	15.1
75°	11.8
77.5°	9.7
80°	7.5
82.5°	5.4
85°	3.2
87.5°	1.1



TEST NUMBER: P1287107

CATALOG NUMBER: P3AS13R259030D2WDE010 E3DLD1WMH

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0

(END OF REPORT)