

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1287116

Luminaire Tested: P3AS13R259030D2WDE010 E3PHLP1MW

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1287116
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2509-551-7)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R259030D2WDE010 E3PHLP1MW
Description: 3in Adjustable Dim to Warm LED luminaire with, R25 optic, 3000K CCT AND, 90CRI ,
E3PHLP1MW TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 621.0 lumens
Efficiency: N/A
Efficacy: 30.9 lumens/watt
Spacing Criteria (0/90/45): 0.59 / 0.59 / 0.65
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 20.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1287116

CATALOG NUMBER: P3AS13R259030D2WDE010 E3PHLP1MW

Luminous Intensity Polar Plot



TEST NUMBER: P1287116

CATALOG NUMBER: P3AS13R259030D2WDE010 E3PHLP1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	112	108	105	102	109	106	103	101	102	100	97		98	96	95		95
2	105	99	94	90	103	97	93	89	94	90	87		91	88	85		88
3	99	91	85	80	97	90	84	80	87	82	78		84	80	77		82
4	93	84	78	73	91	83	77	73	81	76	72		79	74	71		77
5	88	79	72	67	86	78	71	67	76	70	66		74	69	66		72
6	84	74	67	62	82	73	66	62	71	66	61		70	65	61		68
7	79	69	63	58	78	68	62	58	67	61	57		66	61	57		65
8	76	65	59	54	74	65	58	54	63	58	54		62	57	54		61
9	72	62	55	51	71	61	55	51	60	55	51		59	54	51		58
10	69	59	52	48	68	58	52	48	57	52	48		56	51	48		56

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	208667
5°	197138
10°	167554
15°	132714
20°	100855
25°	75246
30°	54717
35°	38708
40°	26249
45°	18327
50°	15385
55°	14872
60°	15700
65°	16137
70°	15964
75°	17114
80°	19573
85°	19625

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 82.5°

Luminance: 20832 cd/sqm

TEST NUMBER: P1287116

CATALOG NUMBER: P3AS13R259030D2WDE010 E3PHLP1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	80.8	13.0
10°-20°	161.8	26.1
20°-30°	143.3	23.1
30°-40°	91.3	14.7
40°-50°	48.3	7.8
50°-60°	35.5	5.7
60°-70°	30.2	4.9
70°-80°	21.3	3.4
80°-90°	8.4	1.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	385.9	62.1
0°-40°	477.2	76.8
0°-60°	561.0	90.3
0°-90°	621.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	621.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	952	
5°	896	81
15°	585	162
25°	311	143
35°	145	91
45°	59	48
55°	39	36
65°	31	30
75°	20	21
85°	8	8
90°	0	

TEST NUMBER: P1287116

CATALOG NUMBER: P3AS13R259030D2WDE010 E3PHLP1MW

CANDELA DISTRIBUTION (FULL):

0°	
0°	951.6
2.5°	937.6
5°	895.6
7.5°	830.3
10°	752.5
12.5°	668.6
15°	584.6
17.5°	503.8
20°	432.2
22.5°	366.9
25°	311.0
27.5°	261.2
30°	216.1
32.5°	177.2
35°	144.6
37.5°	115.1
40°	91.7
42.5°	73.1
45°	59.1
47.5°	51.3
50°	45.1
52.5°	42.0
55°	38.9
57.5°	37.3
60°	35.8
62.5°	32.7
65°	31.1
67.5°	28.0
70°	24.9
72.5°	23.3
75°	20.2
77.5°	17.1
80°	15.5
82.5°	12.4
85°	7.8
87.5°	3.1
90°	0.0

(END OF REPORT)