

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1288184

Luminaire Tested: P3AS05R20W2N902750DE010 E3PH1MW_2700K

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1288184
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2509-551-2)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS05R20W2N902750DE010 E3PH1MW_2700K
Description: 3in Adjustable Tunable White LED luminaire with, R20 optic, 2700K CCT AND, 90CRI ,
E3PH1MW TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 324.0 lumens
Efficiency: N/A
Efficacy: 54.9 lumens/watt
Spacing Criteria (0/90/45): 0.32 / 0.32 / 0.32
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 5.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1288184

CATALOG NUMBER: P3AS05R20W2N902750DE010 E3PH1MW_2700K

Luminous Intensity Polar Plot





TEST NUMBER: P1288184

CATALOG NUMBER: P3AS05R20W2N902750DE010 E3PH1MW_2700K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10		0			
RCR																										
0	119	119	119	119		116	116	116	116		111	111	111		106	106	106		102	102	102		100			
1	116	114	112	111		113	112	110	109		108	107	106		104	104	103		101	100	100		98			
2	113	110	107	105		111	108	106	104		105	104	102		102	101	100		100	99	98		97			
3	110	107	104	101		109	105	103	101		103	101	99		101	99	98		99	97	96		95			
4	108	104	101	98		107	103	100	98		101	98	97		99	97	95		97	96	94		93			
5	106	101	98	96		105	100	97	95		99	96	94		97	95	94		96	94	93		92			
6	104	99	96	93		103	98	95	93		97	94	93		96	94	92		95	93	91		91			
7	102	97	94	92		101	96	93	91		95	93	91		95	92	90		94	92	90		89			
8	100	95	92	90		99	95	92	90		94	91	89		93	91	89		92	90	89		88			
9	99	94	90	88		98	93	90	88		92	90	88		92	89	88		91	89	88		87			
10	97	92	89	87		96	92	89	87		91	88	87		91	88	87		90	88	86		86			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	644269
5°	494848
10°	304871
15°	88718
20°	11831
25°	3508
30°	1038
35°	134
40°	143
45°	0
50°	0
55°	0
60°	0
65°	0
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 0 cd/sqm

TEST NUMBER: P1288184

CATALOG NUMBER: P3AS05R20W2N902750DE010 E3PH1MW_2700K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	187.2	57.8
10°-20°	127.7	39.4
20°-30°	8.2	2.5
30°-40°	0.8	0.2
40°-50°	0.0	0.0
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	323.1	99.7
0°-40°	323.9	100.0
0°-60°	324.0	100.0
0°-90°	324.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	324.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2938	
5°	2248	187
15°	391	128
25°	14	8
35°	0	1
45°	0	0
55°	0	0
65°	0	0
75°	0	0
85°	0	0
90°	0	

TEST NUMBER: P1288184

CATALOG NUMBER: P3AS05R20W2N902750DE010 E3PH1MW_2700K

CANDELA DISTRIBUTION (FULL):

0°	
0°	2938.1
2.5°	2649.3
5°	2248.1
7.5°	1803.5
10°	1369.2
12.5°	858.8
15°	390.8
17.5°	123.7
20°	50.7
22.5°	26.9
25°	14.5
27.5°	7.2
30°	4.1
32.5°	2.1
35°	0.5
37.5°	0.5
40°	0.5
42.5°	0.0
45°	0.0
47.5°	0.0
50°	0.0
52.5°	0.0
55°	0.0
57.5°	0.0
60°	0.0
62.5°	0.0
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)