

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1287128

Luminaire Tested: P3AS13R309030D2WDE010 E3DL1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1287128
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-15)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R309030D2WDE010 E3DL1GPH
Description: 3in Adjustable Dim to Warm LED luminaire with, R30 optic, 3000K CCT AND, 90CRI ,
E3DL1GPH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 559.0 lumens
Efficiency: N/A
Efficacy: 27.8 lumens/watt
Spacing Criteria (0/90/45): 0.54 / 0.54 / 0.54
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 20.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1287128

CATALOG NUMBER: P3AS13R309030D2WDE010 E3DL1GPH

Luminous Intensity Polar Plot



TEST NUMBER: P1287128

CATALOG NUMBER: P3AS13R309030D2WDE010 E3DL1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10			0
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	114	112	110	108	112	110	108	106	106	104	103		102	101	100		99	98	97	95
2	110	105	102	99	107	104	101	98	101	98	96		98	96	94		95	93	92	90
3	105	100	96	92	103	98	95	91	96	93	90		94	91	89		91	89	87	86
4	101	95	90	87	99	94	89	86	92	88	85		90	87	84		88	85	83	82
5	97	90	85	82	96	89	85	81	88	84	81		86	83	80		85	82	79	78
6	94	86	81	78	92	85	81	77	84	80	77		83	79	76		81	78	76	75
7	90	82	77	74	89	82	77	74	81	76	73		80	76	73		78	75	73	71
8	87	79	74	71	86	79	74	71	78	73	70		77	73	70		76	72	70	69
9	84	76	71	68	83	75	71	68	75	70	67		74	70	67		73	70	67	66
10	81	73	68	65	80	73	68	65	72	68	65		71	67	65		71	67	65	63

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	326202
5°	310477
10°	261140
15°	188333
20°	116817
25°	66439
30°	36892
35°	20077
40°	10591
45°	5737
50°	3070
55°	2026
60°	1842
65°	1920
70°	1667
75°	1356
80°	1389
85°	1258

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 5737 cd/sqm

TEST NUMBER: P1287128

CATALOG NUMBER: P3AS13R309030D2WDE010 E3DL1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	127.0	22.7
10°-20°	225.8	40.4
20°-30°	130.5	23.3
30°-40°	49.5	8.9
40°-50°	15.2	2.7
50°-60°	5.1	0.9
60°-70°	3.5	0.6
70°-80°	1.9	0.3
80°-90°	0.6	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	483.2	86.4
0°-40°	532.8	95.3
0°-60°	553.1	98.9
0°-90°	559.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	559.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1488	
5°	1410	127
15°	830	226
25°	275	130
35°	75	50
45°	18	15
55°	5	5
65°	4	3
75°	2	2
85°	0	1
90°	0	

TEST NUMBER: P1287128

CATALOG NUMBER: P3AS13R309030D2WDE010 E3DL1GPH

CANDELA DISTRIBUTION (FULL):

0°	
0°	1487.6
1°	1486.5
2°	1477.5
3°	1460.6
4°	1439.5
5°	1410.5
6°	1373.5
7°	1332.3
8°	1286.4
9°	1231.5
10°	1172.8
11°	1109.5
12°	1042.4
13°	972.2
14°	900.9
15°	829.6
17.5°	654.3
20°	500.6
22.5°	371.2
25°	274.6
27.5°	199.6
30°	145.7
32.5°	105.1
35°	75.0
37.5°	52.3
40°	37.0
42.5°	25.9
45°	18.5
47.5°	12.7
50°	9.0
52.5°	6.3
55°	5.3
57.5°	4.8
60°	4.2
62.5°	3.7
65°	3.7
67.5°	3.2
70°	2.6
72.5°	2.1
75°	1.6
77.5°	1.6
80°	1.1
82.5°	1.1
85°	0.5
87.5°	0.0



TEST NUMBER: P1287128

CATALOG NUMBER: P3AS13R309030D2WDE010 E3DL1GPH

CANDELA DISTRIBUTION (continued):



(END OF REPORT)