

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1287140

Luminaire Tested: P3AS13R309030D2WDE010 E3DLP1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1287140
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-13)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R309030D2WDE010 E3DLP1GPH
Description: 3in Adjustable Dim to Warm LED luminaire with, R30 optic, 3000K CCT AND, 90CRI ,
E3DLP1GPH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 340.0 lumens
Efficiency: N/A
Efficacy: 16.9 lumens/watt
Spacing Criteria (0/90/45): 0.66 / 0.66 / 0.7
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 20.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1287140
CATALOG NUMBER: P3AS13R309030D2WDE010 E3DLP1GPH

Luminous Intensity Polar Plot





TEST NUMBER: P1287140
 CATALOG NUMBER: P3AS13R309030D2WDE010 E3DLP1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	113	110	108	105	111	108	106	104	104	102	100	100	99	97	97	96	95	93				93
2	107	102	98	95	105	101	97	94	97	94	92	94	92	90	92	90	88	86				86
3	102	95	90	86	100	94	89	85	91	87	84	89	86	83	87	84	82	80				80
4	97	89	84	79	95	88	83	79	86	81	78	84	80	77	82	79	76	74				74
5	92	84	78	73	90	83	77	73	81	76	72	79	75	72	78	74	71	70				70
6	88	79	73	68	86	78	72	68	76	71	68	75	71	67	74	70	67	65				65
7	83	74	68	64	82	74	68	64	72	67	63	71	67	63	70	66	63	61				61
8	80	70	64	60	78	70	64	60	69	63	60	67	63	60	67	62	59	58				58
9	76	67	61	57	75	66	60	57	65	60	56	64	60	56	63	59	56	55				55
10	73	63	58	54	72	63	57	54	62	57	53	61	57	53	60	56	53	52				52

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	116175
5°	112568
10°	101423
15°	83905
20°	64966
25°	48729
30°	35373
35°	23557
40°	14484
45°	8497
50°	5219
55°	4244
60°	3684
65°	3009
70°	2693
75°	2711
80°	2020
85°	2768

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 8497 cd/sqm



TEST NUMBER: P1287140

CATALOG NUMBER: P3AS13R309030D2WDE010 E3DLP1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	47.0	13.8
10°-20°	101.8	29.9
20°-30°	92.6	27.2
30°-40°	56.0	16.5
40°-50°	22.5	6.6
50°-60°	9.9	2.9
60°-70°	6.0	1.8
70°-80°	3.3	1.0
80°-90°	1.0	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	241.4	71.0
0°-40°	297.4	87.5
0°-60°	329.8	97.0
0°-90°	340.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	340.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	530	
5°	511	47
15°	370	102
25°	201	93
35°	88	56
45°	27	22
55°	11	10
65°	6	6
75°	3	3
85°	1	1
90°	0	



TEST NUMBER: P1287140
CATALOG NUMBER: P3AS13R309030D2WDE010 E3DLP1GPH

CANDELA DISTRIBUTION (FULL):

0°	
0°	529.8
1°	529.3
2°	527.2
3°	523.5
4°	518.2
5°	511.4
6°	503.0
7°	494.0
8°	482.4
9°	469.2
10°	455.5
11°	439.7
12°	422.8
13°	405.9
14°	387.5
15°	369.6
17.5°	322.7
20°	278.4
22.5°	237.2
25°	201.4
27.5°	168.7
30°	139.7
32.5°	112.8
35°	88.0
37.5°	67.5
40°	50.6
42.5°	36.9
45°	27.4
47.5°	20.6
50°	15.3
52.5°	12.1
55°	11.1
57.5°	9.5
60°	8.4
62.5°	6.9
65°	5.8
67.5°	5.3
70°	4.2
72.5°	3.7
75°	3.2
77.5°	2.6
80°	1.6
82.5°	1.1
85°	1.1
87.5°	0.5



TEST NUMBER: P1287140
CATALOG NUMBER: P3AS13R309030D2WDE010 E3DLP1GPH

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0

(END OF REPORT)