

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1287150

Luminaire Tested: P3AS13R359030D2WDE010 E3CB1MMS

Issue Date: 1/30/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1287150  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-20)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS13R359030D2WDE010 E3CB1MMS  
Description: 3in Adjustable Dim to Warm LED luminaire with, R35 optic, 3000K CCT AND, 90CRI ,  
E3CB1MMS TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1367.1 lumens  
Efficiency: N/A  
Efficacy: 68.0 lumens/watt  
Spacing Criteria (0/90/45): 0.58 / 0.58 / 0.52  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 20.1  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1287150  
CATALOG NUMBER: P3AS13R359030D2WDE010 E3CB1MMS

### Luminous Intensity Polar Plot





TEST NUMBER: P1287150  
 CATALOG NUMBER: P3AS13R359030D2WDE010 E3CB1MMS

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	115	113	111	109	112	110	109	107	106	105	104	103	102	101	99	99	98	96	96	96	96
2	111	107	104	101	109	105	103	100	102	100	98	99	98	96	97	95	94	93	93	93	93
3	107	102	98	95	105	101	97	95	98	96	93	96	94	92	94	92	90	89	89	89	89
4	104	98	94	91	102	97	93	90	95	92	89	93	90	88	91	89	87	86	86	86	86
5	100	94	90	87	99	93	89	86	92	88	86	90	87	85	89	86	84	83	83	83	83
6	97	91	86	83	96	90	86	83	89	85	82	87	84	82	86	83	81	80	80	80	80
7	94	87	83	80	93	87	83	80	86	82	79	85	81	79	84	81	79	77	77	77	77
8	91	84	80	77	90	84	80	77	83	79	77	82	79	76	81	78	76	75	75	75	75
9	89	82	77	74	88	81	77	74	80	77	74	80	76	74	79	76	74	73	73	73	73
10	86	79	75	72	85	79	75	72	78	74	72	77	74	72	77	74	71	70	70	70	70

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	891376
5°	873209
10°	812365
15°	595577
20°	304970
25°	109918
30°	42791
35°	14991
40°	6154
45°	1675
50°	1467
55°	1644
60°	1403
65°	1141
70°	1410
75°	1864
80°	1389
85°	0

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 75°  
 Luminance: 1864 cd/sqm



TEST NUMBER: P1287150

CATALOG NUMBER: P3AS13R359030D2WDE010 E3CB1MMS

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	369.8	27.1
10°-20°	693.9	50.8
20°-30°	245.7	18.0
30°-40°	43.0	3.1
40°-50°	6.3	0.5
50°-60°	3.5	0.3
60°-70°	2.5	0.2
70°-80°	1.9	0.1
80°-90°	0.4	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1309.4	95.8
0°-40°	1352.4	98.9
0°-60°	1362.2	99.6
0°-90°	1367.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1367.1	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	4065	
5°	3967	370
15°	2624	694
25°	454	246
35°	56	43
45°	5	6
55°	4	3
65°	2	3
75°	2	2
85°	0	0
90°	0	



TEST NUMBER: P1287150  
CATALOG NUMBER: P3AS13R359030D2WDE010 E3CB1MMS

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	4065.0
1°	4063.9
2°	4051.0
3°	4026.2
4°	4003.6
5°	3967.0
6°	3929.3
7°	3887.4
8°	3835.7
9°	3755.0
10°	3648.4
11°	3500.9
12°	3323.3
13°	3112.3
14°	2879.7
15°	2623.5
17.5°	1953.9
20°	1306.9
22.5°	788.0
25°	454.3
27.5°	271.3
30°	169.0
32.5°	98.0
35°	56.0
37.5°	35.5
40°	21.5
42.5°	10.8
45°	5.4
47.5°	4.3
50°	4.3
52.5°	4.3
55°	4.3
57.5°	3.2
60°	3.2
62.5°	3.2
65°	2.2
67.5°	2.2
70°	2.2
72.5°	2.2
75°	2.2
77.5°	1.1
80°	1.1
82.5°	1.1
85°	0.0
87.5°	0.0



TEST NUMBER: P1287150  
CATALOG NUMBER: P3AS13R359030D2WDE010 E3CB1MMS

CANDELA DISTRIBUTION (continued):

0°  
90° | 0.0

(END OF REPORT)