

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1287235

Luminaire Tested: P3AS13R509030D2WDE010 E3CD1MMS

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1287235
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-32)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R509030D2WDE010 E3CD1MMS
Description: 3in Adjustable Dim to Warm LED luminaire with, R50 optic, 3000K CCT AND, 90CRI ,
E3CD1MMS TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1474.1 lumens
Efficiency: N/A
Efficacy: 73.3 lumens/watt
Spacing Criteria (0/90/45): 0.84 / 0.84 / 0.76
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 20.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1287235
CATALOG NUMBER: P3AS13R509030D2WDE010 E3CD1MMS

Luminous Intensity Polar Plot





TEST NUMBER: P1287235
 CATALOG NUMBER: P3AS13R509030D2WDE010 E3CD1MMS

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	102	102	102	100
1	114	112	109	107	112	109	107	106	105	104	102	102	101	99	98	97	96	96	96	96	95
2	109	105	101	98	107	103	100	97	100	97	95	97	95	93	94	93	91	91	91	91	90
3	105	99	95	91	103	98	94	90	95	92	89	93	90	88	91	88	86	86	86	86	85
4	100	94	89	85	99	92	88	85	90	87	84	88	85	83	87	84	82	82	82	82	80
5	96	89	84	80	94	88	83	79	86	82	79	84	81	78	83	80	77	77	77	77	76
6	92	84	79	75	91	83	79	75	82	78	74	81	77	74	79	76	73	73	73	73	72
7	88	80	75	71	87	79	74	71	78	74	71	77	73	70	76	73	70	70	70	70	69
8	85	76	71	67	83	76	71	67	75	70	67	74	70	67	73	69	66	66	66	66	65
9	81	73	68	64	80	72	67	64	71	67	64	71	66	63	70	66	63	63	63	63	62
10	78	69	64	61	77	69	64	61	68	64	61	68	63	61	67	63	60	60	60	60	59

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	513358
5°	504159
10°	484093
15°	443907
20°	391427
25°	300017
30°	163139
35°	52494
40°	12337
45°	1675
50°	1467
55°	1644
60°	1403
65°	1660
70°	1410
75°	1864
80°	1389
85°	2768

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 85°
 Luminance: 2768 cd/sqm



TEST NUMBER: P1287235

CATALOG NUMBER: P3AS13R509030D2WDE010 E3CD1MMS

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	214.9	14.6
10°-20°	543.5	36.9
20°-30°	544.4	36.9
30°-40°	153.1	10.4
40°-50°	9.3	0.6
50°-60°	3.5	0.2
60°-70°	2.8	0.2
70°-80°	1.9	0.1
80°-90°	0.7	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1302.8	88.4
0°-40°	1455.9	98.8
0°-60°	1468.6	99.6
0°-90°	1474.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1474.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2341	
5°	2290	215
15°	1955	544
25°	1240	544
35°	196	153
45°	5	9
55°	4	3
65°	3	3
75°	2	2
85°	1	1
90°	0	



TEST NUMBER: P1287235
CATALOG NUMBER: P3AS13R509030D2WDE010 E3CD1MMS

CANDELA DISTRIBUTION (FULL):

0°	
0°	2341.1
2.5°	2329.2
5°	2290.4
7.5°	2237.6
10°	2174.1
12.5°	2078.2
15°	1955.4
17.5°	1814.2
20°	1677.4
22.5°	1507.2
25°	1240.0
27.5°	923.3
30°	644.3
32.5°	388.9
35°	196.1
37.5°	92.7
40°	43.1
42.5°	16.2
45°	5.4
47.5°	4.3
50°	4.3
52.5°	4.3
55°	4.3
57.5°	3.2
60°	3.2
62.5°	3.2
65°	3.2
67.5°	2.2
70°	2.2
72.5°	2.2
75°	2.2
77.5°	1.1
80°	1.1
82.5°	1.1
85°	1.1
87.5°	0.0
90°	0.0

(END OF REPORT)