

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1288349

Luminaire Tested: P3AS05R20W2N902765DE010 E3PHLP1MW\_2700K

Issue Date: 1/29/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1288349  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2509-551-6)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/29/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS05R20W2N902765DE010 E3PHLP1MW\_2700K  
Description: 3in Adjustable Tunable White LED luminaire with, R20 optic, 2700K CCT AND, 90CRI ,  
E3PHLP1MW TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 176.0 lumens  
Efficiency: N/A  
Efficacy: 29.8 lumens/watt  
Spacing Criteria (0/90/45): 0.55 / 0.55 / 0.63  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 5.9  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1288349  
CATALOG NUMBER: P3AS05R20W2N902765DE010 E3PHLP1MW\_2700K

### Luminous Intensity Polar Plot





TEST NUMBER: P1288349

CATALOG NUMBER: P3AS05R20W2N902765DE010 E3PHLP1MW\_2700K

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	112	108	105	102	109	106	103	101	102	100	97	98	96	95	95	93	92	90	90	90	90
2	105	99	94	90	103	97	93	89	94	90	87	91	88	85	88	85	83	81	81	81	81
3	99	91	85	80	97	90	84	80	87	82	78	84	80	77	82	79	76	74	74	74	74
4	93	84	78	73	91	83	77	73	81	76	72	79	74	71	77	73	70	68	68	68	68
5	88	79	72	67	86	78	71	67	76	70	66	74	69	66	72	68	65	63	63	63	63
6	84	74	67	62	82	73	66	62	71	66	61	70	65	61	68	64	61	59	59	59	59
7	79	69	63	58	78	68	62	58	67	62	57	66	61	57	65	60	57	55	55	55	55
8	76	65	59	54	74	65	58	54	64	58	54	62	57	54	61	57	53	52	52	52	52
9	72	62	55	51	71	61	55	51	60	55	51	59	54	51	58	54	50	49	49	49	49
10	69	59	52	48	68	58	52	48	57	52	48	57	52	48	56	51	48	46	46	46	46

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	62583
5°	58375
10°	48452
15°	37049
20°	27792
25°	20929
30°	15471
35°	10815
40°	7414
45°	5148
50°	4435
55°	4358
60°	4561
65°	4566
70°	4680
75°	4829
80°	5177
85°	5284

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 82.5°  
 Luminance: 6048 cd/sqm



TEST NUMBER: P1288349

CATALOG NUMBER: P3AS05R20W2N902765DE010 E3PHLP1MW\_2700K

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	23.8	13.5
10°-20°	45.4	25.8
20°-30°	39.9	22.7
30°-40°	25.7	14.6
40°-50°	13.7	7.8
50°-60°	10.3	5.8
60°-70°	8.7	5.0
70°-80°	6.2	3.5
80°-90°	2.4	1.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	109.0	62.0
0°-40°	134.8	76.6
0°-60°	158.7	90.2
0°-90°	176.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	176.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	285	
5°	265	24
15°	163	45
25°	86	40
35°	40	26
45°	17	14
55°	11	10
65°	9	9
75°	6	6
85°	2	2
90°	0	



TEST NUMBER: P1288349

CATALOG NUMBER: P3AS05R20W2N902765DE010 E3PHLP1MW\_2700K

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	285.4
2.5°	279.7
5°	265.2
7.5°	242.9
10°	217.6
12.5°	189.6
15°	163.2
17.5°	139.3
20°	119.1
22.5°	102.0
25°	86.5
27.5°	73.0
30°	61.1
32.5°	50.2
35°	40.4
37.5°	32.6
40°	25.9
42.5°	20.7
45°	16.6
47.5°	14.5
50°	13.0
52.5°	11.9
55°	11.4
57.5°	10.9
60°	10.4
62.5°	9.3
65°	8.8
67.5°	8.3
70°	7.3
72.5°	6.7
75°	5.7
77.5°	5.2
80°	4.1
82.5°	3.6
85°	2.1
87.5°	1.0
90°	0.0

(END OF REPORT)