

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1287274

Luminaire Tested: P3AS13R559030D2WDE010 E3DL1MW

Issue Date: 1/30/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1287274  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-35)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS13R559030D2WDE010 E3DL1MW  
Description: 3in Adjustable Dim to Warm LED luminaire with, R55 optic, 3000K CCT AND, 90CRI , E3DL1M  
TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1173.0 lumens  
Efficiency: N/A  
Efficacy: 58.4 lumens/watt  
Spacing Criteria (0/90/45): 0.83 / 0.83 / 0.81  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 20.1  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1287274  
CATALOG NUMBER: P3AS13R559030D2WDE010 E3DL1MW

### Luminous Intensity Polar Plot





TEST NUMBER: P1287274  
 CATALOG NUMBER: P3AS13R559030D2WDE010 E3DL1MW

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	113	111	108	106	111	108	106	104	104	103	101	101	99	98	97	96	95	93			
2	108	103	99	95	106	101	97	94	98	95	92	95	92	90	92	90	88	87			
3	102	96	91	87	100	94	90	86	92	88	85	89	86	83	87	85	82	81			
4	97	90	84	80	95	89	83	79	86	82	78	84	81	78	82	79	77	75			
5	92	84	78	74	91	83	78	74	81	77	73	80	76	72	78	75	72	70			
6	88	79	73	69	86	78	73	68	77	72	68	75	71	68	74	70	67	66			
7	84	74	68	64	82	74	68	64	72	67	64	71	67	63	70	66	63	62			
8	80	70	64	60	78	70	64	60	69	63	60	67	63	60	67	62	59	58			
9	76	66	61	57	75	66	60	56	65	60	56	64	59	56	63	59	56	55			
10	73	63	57	53	72	62	57	53	62	57	53	61	56	53	60	56	53	52			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	322101
5°	318819
10°	307899
15°	284610
20°	245581
25°	193971
30°	137591
35°	88713
40°	53300
45°	30019
50°	16136
55°	5773
60°	5175
65°	5033
70°	4809
75°	4575
80°	4041
85°	2768

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 30019 cd/sqm



TEST NUMBER: P1287274

CATALOG NUMBER: P3AS13R559030D2WDE010 E3DL1MW

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	136.2	11.6
10°-20°	346.7	29.6
20°-30°	363.3	31.0
30°-40°	212.0	18.1
40°-50°	79.3	6.8
50°-60°	18.7	1.6
60°-70°	9.6	0.8
70°-80°	5.7	0.5
80°-90°	1.6	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	846.2	72.1
0°-40°	1058.1	90.2
0°-60°	1156.1	98.6
0°-90°	1173.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1173.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1469	
5°	1448	136
15°	1254	347
25°	802	363
35°	331	212
45°	97	79
55°	15	19
65°	10	10
75°	5	6
85°	1	2
90°	0	



TEST NUMBER: P1287274  
CATALOG NUMBER: P3AS13R559030D2WDE010 E3DL1MW

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	1468.9
2.5°	1464.6
5°	1448.4
7.5°	1422.6
10°	1382.8
12.5°	1326.8
15°	1253.7
17.5°	1161.1
20°	1052.4
22.5°	930.8
25°	801.7
27.5°	669.3
30°	543.4
32.5°	429.4
35°	331.4
37.5°	251.8
40°	186.2
42.5°	133.4
45°	96.8
47.5°	69.9
50°	47.3
52.5°	26.9
55°	15.1
57.5°	12.9
60°	11.8
62.5°	10.8
65°	9.7
67.5°	8.6
70°	7.5
72.5°	6.5
75°	5.4
77.5°	4.3
80°	3.2
82.5°	2.2
85°	1.1
87.5°	1.1
90°	0.0

(END OF REPORT)