

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1288385

Luminaire Tested: P3AS05R25W2N902750DE010 E3D1H_2700K

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1288385
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2501-338-9)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS05R25W2N902750DE010 E3D1H_2700K
Description: 3in Adjustable Tunable White LED luminaire with, R25 optic, 2700K CCT AND, 90CRI , E3D1H TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 485.0 lumens
Efficiency: N/A
Efficacy: 82.2 lumens/watt
Spacing Criteria (0/90/45): 0.44 / 0.44 / 0.4
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 5.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1288385

CATALOG NUMBER: P3AS05R25W2N902750DE010 E3D1H_2700K

Luminous Intensity Polar Plot





TEST NUMBER: P1288385

CATALOG NUMBER: P3AS05R25W2N902750DE010 E3D1H_2700K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	196.5	40.5
10°-20°	223.5	46.1
20°-30°	51.9	10.7
30°-40°	10.9	2.2
40°-50°	1.8	0.4
50°-60°	0.3	0.1
60°-70°	0.2	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	471.9	97.3
0°-40°	482.8	99.5
0°-60°	484.9	100.0
0°-90°	485.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	485.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2422	
5°	2235	196
15°	801	223
25°	104	52
35°	16	11
45°	2	2
55°	0	0
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P1288385

CATALOG NUMBER: P3AS05R25W2N902750DE010 E3D1H_2700K

CANDELA DISTRIBUTION (FULL):

0°	
0°	2422.3
1°	2417.4
2°	2392.2
3°	2356.9
4°	2302.9
5°	2235.4
6°	2148.7
7°	2058.0
8°	1956.1
9°	1841.3
10°	1709.8
11°	1557.3
12°	1382.3
13°	1190.7
14°	990.2
15°	801.0
16°	633.6
17°	493.6
18°	388.3
19°	310.5
20°	256.9
21°	214.7
22°	180.2
23°	150.5
24°	125.9
25°	104.5
27.5°	61.9
30°	38.7
32.5°	24.8
35°	15.8
37.5°	9.5
40°	4.9
42.5°	3.2
45°	2.1
47.5°	1.2
50°	0.7
52.5°	0.4
55°	0.4
57.5°	0.2
60°	0.2
62.5°	0.2
65°	0.2
67.5°	0.2
70°	0.0
72.5°	0.0



TEST NUMBER: P1288385

CATALOG NUMBER: P3AS05R25W2N902750DE010 E3D1H_2700K

CANDELA DISTRIBUTION (continued):

	0°
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)