

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1287317

Luminaire Tested: P3AS13R609030D2WDE010 E3DLP1WMH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1287317
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-37)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R609030D2WDE010 E3DLP1WMH
Description: 3in Adjustable Dim to Warm LED luminaire with, R60 optic, 3000K CCT AND, 90CRI ,
E3DLP1WMH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 783.0 lumens
Efficiency: N/A
Efficacy: 39.0 lumens/watt
Spacing Criteria (0/90/45): 0.79 / 0.79 / 0.83
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 20.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1287317

CATALOG NUMBER: P3AS13R609030D2WDE010 E3DLP1WMH

Luminous Intensity Polar Plot



TEST NUMBER: P1287317

CATALOG NUMBER: P3AS13R609030D2WDE010 E3DLP1WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	107	105	110	108	105	103	104	102	100		100	98	97		96
2	107	101	97	93	104	100	96	92	96	93	90		93	91	88		91
3	101	94	88	84	99	92	87	83	90	86	82		87	84	81		85
4	95	87	81	77	93	86	80	76	84	79	75		82	78	74		80
5	90	81	75	70	88	80	74	70	78	73	69		77	72	69		75
6	85	76	69	65	84	75	69	65	73	68	64		72	67	64		71
7	81	71	65	60	79	70	64	60	69	64	60		68	63	59		67
8	77	67	60	56	75	66	60	56	65	60	56		64	59	55		63
9	73	63	57	52	72	62	56	52	61	56	52		60	55	52		60
10	69	59	53	49	68	59	53	49	58	53	49		57	52	49		56

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	198427
5°	193990
10°	181604
15°	162929
20°	140106
25°	115845
30°	91533
35°	67967
40°	46831
45°	29367
50°	16136
55°	9443
60°	8508
65°	7264
70°	6219
75°	6354
80°	5430
85°	5535

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 29367 cd/sqm

TEST NUMBER: P1287317

CATALOG NUMBER: P3AS13R609030D2WDE010 E3DLP1WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	82.0	10.5
10°-20°	199.3	25.5
20°-30°	218.6	27.9
30°-40°	159.3	20.3
40°-50°	75.2	9.6
50°-60°	24.6	3.1
60°-70°	13.9	1.8
70°-80°	7.5	1.0
80°-90°	2.4	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	500.0	63.9
0°-40°	659.3	84.2
0°-60°	759.2	97.0
0°-90°	783.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	783.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	905	
5°	881	82
15°	718	199
25°	479	219
35°	254	159
45°	95	75
55°	25	25
65°	14	14
75°	8	8
85°	2	2
90°	0	

TEST NUMBER: P1287317

CATALOG NUMBER: P3AS13R609030D2WDE010 E3DLP1WMH

CANDELA DISTRIBUTION (FULL):

0°	
0°	904.9
2.5°	899.6
5°	881.3
7.5°	853.3
10°	815.6
12.5°	770.4
15°	717.7
17.5°	660.7
20°	600.4
22.5°	539.1
25°	478.8
27.5°	418.6
30°	361.5
32.5°	306.7
35°	253.9
37.5°	206.6
40°	163.6
42.5°	125.9
45°	94.7
47.5°	68.9
50°	47.3
52.5°	31.2
55°	24.7
57.5°	21.5
60°	19.4
62.5°	16.1
65°	14.0
67.5°	11.8
70°	9.7
72.5°	8.6
75°	7.5
77.5°	5.4
80°	4.3
82.5°	3.2
85°	2.2
87.5°	1.1
90°	0.0

(END OF REPORT)