

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1288585

Luminaire Tested: P3AS05R25W2N902765DE010 E3DL1GPH_5000K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1288585
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-11)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS05R25W2N902765DE010 E3DL1GPH_5000K
Description: 3in Adjustable Tunable White LED luminaire with, R25 optic, 5000K CCT AND, 90CRI ,
E3DL1GPH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 205.1 lumens
Efficiency: N/A
Efficacy: 34.8 lumens/watt
Spacing Criteria (0/90/45): 0.49 / 0.49 / 0.51
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 5.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1288585

CATALOG NUMBER: P3AS05R25W2N902765DE010 E3DL1GPH_5000K

Luminous Intensity Polar Plot



TEST NUMBER: P1288585

CATALOG NUMBER: P3AS05R25W2N902765DE010 E3DL1GPH_5000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111		106	106	106		102	102	102
1	114	112	110	108		112	110	108	106		106	104	103		102	101	100		99	98	97
2	110	105	102	99		107	104	101	98		101	98	96		98	96	94		95	93	92
3	105	100	96	92		103	98	95	91		96	93	90		94	91	89		91	89	87
4	101	95	90	87		99	94	89	86		92	88	85		90	87	84		88	85	83
5	97	90	85	82		96	89	85	81		88	84	81		86	83	80		85	82	79
6	94	86	81	78		92	86	81	77		84	80	77		83	79	76		82	78	76
7	90	83	78	74		89	82	77	74		81	77	74		80	76	73		79	75	73
8	87	79	74	71		86	79	74	71		78	74	71		77	73	70		76	73	70
9	84	76	71	68		83	76	71	68		75	71	68		74	70	68		73	70	67
10	81	73	69	65		80	73	68	65		72	68	65		72	68	65		71	67	65

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	131503
5°	122694
10°	98284
15°	66720
20°	40370
25°	23614
30°	13445
35°	7388
40°	3922
45°	2078
50°	1194
55°	918
60°	789
65°	830
70°	769
75°	678
80°	505
85°	503

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 2078 cd/sqm

TEST NUMBER: P1288585

CATALOG NUMBER: P3AS05R25W2N902765DE010 E3DL1GPH_5000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	49.5	24.1
10°-20°	80.8	39.4
20°-30°	46.2	22.5
30°-40°	18.2	8.9
40°-50°	5.6	2.7
50°-60°	2.2	1.1
60°-70°	1.5	0.7
70°-80°	0.8	0.4
80°-90°	0.3	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	176.4	86.0
0°-40°	194.6	94.9
0°-60°	202.4	98.7
0°-90°	205.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	205.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	600	
5°	557	49
15°	294	81
25°	98	46
35°	28	18
45°	7	6
55°	2	2
65°	2	2
75°	1	1
85°	0	0
90°	0	

TEST NUMBER: P1288585

CATALOG NUMBER: P3AS05R25W2N902765DE010 E3DL1GPH_5000K

CANDELA DISTRIBUTION (FULL):

0°	
0°	599.7
1°	598.5
2°	593.6
3°	585.0
4°	573.0
5°	557.4
6°	539.0
7°	518.2
8°	494.1
9°	469.4
10°	441.4
11°	413.8
12°	383.4
13°	353.4
14°	322.7
15°	293.9
17.5°	227.8
20°	173.0
22.5°	129.9
25°	97.6
27.5°	72.3
30°	53.1
32.5°	38.4
35°	27.6
37.5°	19.6
40°	13.7
42.5°	9.4
45°	6.7
47.5°	4.7
50°	3.5
52.5°	2.7
55°	2.4
57.5°	2.2
60°	1.8
62.5°	1.6
65°	1.6
67.5°	1.4
70°	1.2
72.5°	1.0
75°	0.8
77.5°	0.6
80°	0.4
82.5°	0.4
85°	0.2
87.5°	0.2



TEST NUMBER: P1288585

CATALOG NUMBER: P3AS05R25W2N902765DE010 E3DL1GPH_5000K

CANDELA DISTRIBUTION (continued):



(END OF REPORT)