

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1287339

Luminaire Tested: P3AS13R659030D2WDE010 E3DLD1WH

Issue Date: 1/30/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1287339  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-42)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS13R659030D2WDE010 E3DLD1WH  
Description: 3in Adjustable Dim to Warm LED luminaire with, R65 optic, 3000K CCT AND, 90CRI ,  
E3DLD1WH TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 848.0 lumens  
Efficiency: N/A  
Efficacy: 42.2 lumens/watt  
Spacing Criteria (0/90/45): 0.94 / 0.94 / 1  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 20.1  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1287339  
CATALOG NUMBER: P3AS13R659030D2WDE010 E3DLD1WH

### Luminous Intensity Polar Plot





TEST NUMBER: P1287339  
 CATALOG NUMBER: P3AS13R659030D2WDE010 E3DLD1WH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	112	109	106	103	110	107	104	101	102	100	98	99	97	95	95	94	93	91			
2	105	99	94	90	103	97	93	89	94	90	87	91	88	85	88	86	84	82			
3	99	91	85	80	96	89	84	79	87	82	78	84	80	77	82	78	76	74			
4	92	83	77	72	90	82	76	71	80	75	70	78	73	70	76	72	69	67			
5	87	77	70	65	85	76	69	65	74	68	64	72	67	63	71	66	63	61			
6	82	71	64	59	80	70	64	59	69	63	58	67	62	58	66	61	58	56			
7	77	66	59	54	75	65	59	54	64	58	54	63	57	53	61	57	53	51			
8	72	61	55	50	71	61	54	50	60	54	49	59	53	49	58	53	49	47			
9	68	57	51	46	67	57	50	46	56	50	46	55	49	46	54	49	45	44			
10	65	54	47	43	64	53	47	43	52	47	43	52	46	42	51	46	42	41			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	150909
5°	148866
10°	143885
15°	135687
20°	125148
25°	113619
30°	100623
35°	85635
40°	68128
45°	48098
50°	27905
55°	15216
60°	14166
65°	12868
70°	11733
75°	10929
80°	9471
85°	8051

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 48098 cd/sqm



TEST NUMBER: P1287339

CATALOG NUMBER: P3AS13R659030D2WDE010 E3DLD1WH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	63.6	7.5
10°-20°	167.2	19.7
20°-30°	214.9	25.3
30°-40°	198.8	23.4
40°-50°	120.0	14.2
50°-60°	40.9	4.8
60°-70°	24.6	2.9
70°-80°	13.9	1.6
80°-90°	4.0	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	445.7	52.6
0°-40°	644.5	76.0
0°-60°	805.5	95.0
0°-90°	848.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	848.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	688	
5°	676	64
15°	598	167
25°	470	215
35°	320	199
45°	155	120
55°	40	41
65°	25	25
75°	13	14
85°	3	4
90°	0	

TEST NUMBER: P1287339

CATALOG NUMBER: P3AS13R659030D2WDE010 E3DLD1WH

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	688.2
2.5°	685.0
5°	676.3
7.5°	663.4
10°	646.2
12.5°	624.6
15°	597.7
17.5°	568.6
20°	536.3
22.5°	502.9
25°	469.6
27.5°	434.0
30°	397.4
32.5°	360.8
35°	319.9
37.5°	280.0
40°	238.0
42.5°	196.0
45°	155.1
47.5°	117.4
50°	81.8
52.5°	51.7
55°	39.8
57.5°	35.5
60°	32.3
62.5°	28.0
65°	24.8
67.5°	21.5
70°	18.3
72.5°	16.2
75°	12.9
77.5°	10.8
80°	7.5
82.5°	5.4
85°	3.2
87.5°	2.2
90°	0.0

(END OF REPORT)