

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1288596

Luminaire Tested: P3AS05R25W2N902765DE010 E3DL1LI_4000K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1288596
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-11)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS05R25W2N902765DE010 E3DL1LI_4000K
Description: 3in Adjustable Tunable White LED luminaire with, R25 optic, 4000K CCT AND, 90CRI ,
E3DL1LI TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 420.0 lumens
Efficiency: N/A
Efficacy: 71.2 lumens/watt
Spacing Criteria (0/90/45): 0.49 / 0.49 / 0.51
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 5.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1288596

CATALOG NUMBER: P3AS05R25W2N902765DE010 E3DL1LI_4000K

Luminous Intensity Polar Plot



TEST NUMBER: P1288596

CATALOG NUMBER: P3AS05R25W2N902765DE010 E3DL1LI_4000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20				20				20
RC	80				70				50				30				10				0				0				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																													
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	99	98	97	95	94	93	92	91	90	89	88
1	114	112	110	108	112	110	108	106	106	104	103	102	101	100	99	98	97	95	94	93	92	91	90	89	88	87	86	85	84
2	110	105	102	99	107	104	101	98	101	98	96	98	96	94	95	93	92	90	89	88	87	86	85	84	83	82	81	80	79
3	105	100	96	92	103	98	95	91	96	93	90	94	91	89	91	89	87	86	85	84	83	82	81	80	79	78	77	76	75
4	101	95	90	87	99	94	89	86	92	88	85	90	87	84	88	85	83	82	81	80	79	78	77	76	75	74	73	72	71
5	97	90	85	82	96	89	85	81	88	84	81	86	83	80	85	82	79	78	77	76	75	74	73	72	71	70	69	68	67
6	94	86	81	78	92	86	81	78	84	80	77	83	79	77	82	78	76	75	74	73	72	71	70	69	68	67	66	65	64
7	90	83	78	74	89	82	77	74	81	77	74	80	76	73	79	75	73	72	71	70	69	68	67	66	65	64	63	62	61
8	87	79	74	71	86	79	74	71	78	74	71	77	73	70	76	73	70	69	68	67	66	65	64	63	62	61	60	59	58
9	84	76	71	68	83	76	71	68	75	71	68	74	70	68	73	70	67	66	65	64	63	62	61	60	59	58	57	56	55
10	81	73	69	65	80	73	68	65	72	68	65	72	68	65	71	67	65	64	63	62	61	60	59	58	57	56	55	54	53

AVERAGE LUMINANCE (cd/sqm):

0°	269408
5°	251353
10°	201355
15°	136686
20°	82701
25°	48366
30°	27549
35°	15151
40°	8044
45°	4217
50°	2456
55°	1835
60°	1579
65°	1660
70°	1539
75°	1356
80°	1010
85°	1006

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 4217 cd/sqm

TEST NUMBER: P1288596

CATALOG NUMBER: P3AS05R25W2N902765DE010 E3DL1LI_4000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	101.3	24.1
10°-20°	165.5	39.4
20°-30°	94.6	22.5
30°-40°	37.3	8.9
40°-50°	11.4	2.7
50°-60°	4.5	1.1
60°-70°	3.0	0.7
70°-80°	1.7	0.4
80°-90°	0.5	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	361.4	86.1
0°-40°	398.8	95.0
0°-60°	414.7	98.7
0°-90°	420.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	420.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1229	
5°	1142	101
15°	602	166
25°	200	95
35°	57	37
45°	14	11
55°	5	5
65°	3	3
75°	2	2
85°	0	1
90°	0	

TEST NUMBER: P1288596

CATALOG NUMBER: P3AS05R25W2N902765DE010 E3DL1LI_4000K

CANDELA DISTRIBUTION (FULL):

0°	
0°	1228.6
1°	1226.2
2°	1216.2
3°	1198.5
4°	1174.0
5°	1141.9
6°	1104.2
7°	1061.7
8°	1012.3
9°	961.7
10°	904.3
11°	847.7
12°	785.5
13°	724.1
14°	661.1
15°	602.1
17.5°	466.8
20°	354.4
22.5°	266.1
25°	199.9
27.5°	148.1
30°	108.8
32.5°	78.7
35°	56.6
37.5°	40.1
40°	28.1
42.5°	19.3
45°	13.6
47.5°	9.6
50°	7.2
52.5°	5.6
55°	4.8
57.5°	4.4
60°	3.6
62.5°	3.2
65°	3.2
67.5°	2.8
70°	2.4
72.5°	2.0
75°	1.6
77.5°	1.2
80°	0.8
82.5°	0.8
85°	0.4
87.5°	0.4



TEST NUMBER: P1288596

CATALOG NUMBER: P3AS05R25W2N902765DE010 E3DL1LI_4000K

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0

(END OF REPORT)