

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1287348

Luminaire Tested: P3AS13R709030D2WDE010 E3CB1MMS

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1287348
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-48)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R709030D2WDE010 E3CB1MMS
Description: 3in Adjustable Dim to Warm LED luminaire with, R70 optic, 3000K CCT AND, 90CRI ,
E3CB1MMS TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1347.0 lumens
Efficiency: N/A
Efficacy: 67.0 lumens/watt
Spacing Criteria (0/90/45): 1.01 / 1.01 / 1.03
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 20.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1287348

CATALOG NUMBER: P3AS13R709030D2WDE010 E3CB1MMS

Luminous Intensity Polar Plot



TEST NUMBER: P1287348

CATALOG NUMBER: P3AS13R709030D2WDE010 E3CB1MMS

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	107	105	111	108	106	103	104	102	100		100	99	97		97
2	107	102	97	94	105	100	96	93	97	94	91		94	91	89		91
3	101	94	89	85	99	93	88	84	90	86	83		88	84	81		85
4	95	87	81	77	94	86	81	76	84	79	75		82	78	75		80
5	90	81	75	70	88	80	74	70	78	73	69		77	72	69		75
6	85	75	69	64	83	75	69	64	73	68	64		72	67	63		70
7	80	70	64	59	79	70	64	59	68	63	59		67	62	59		66
8	76	66	59	55	75	65	59	55	64	58	55		63	58	54		62
9	72	62	55	51	71	61	55	51	60	55	51		59	54	50		58
10	68	58	52	47	67	57	51	47	56	51	47		56	51	47		55

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	267479
5°	255227
10°	242837
15°	236346
20°	227613
25°	215432
30°	200360
35°	168298
40°	108489
45°	50424
50°	13236
55°	3288
60°	3289
65°	2802
70°	2757
75°	2711
80°	2778
85°	2768

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 50424 cd/sqm

TEST NUMBER: P1287348

CATALOG NUMBER: P3AS13R709030D2WDE010 E3CB1MMS

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	108.5	8.1
10°-20°	292.5	21.7
20°-30°	408.7	30.3
30°-40°	378.9	28.1
40°-50°	135.9	10.1
50°-60°	11.5	0.9
60°-70°	5.7	0.4
70°-80°	3.7	0.3
80°-90°	1.5	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	809.8	60.1
0°-40°	1188.7	88.2
0°-60°	1336.1	99.2
0°-90°	1347.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1347.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1220	
5°	1160	109
15°	1041	293
25°	890	409
35°	629	379
45°	163	136
55°	9	11
65°	5	6
75°	3	4
85°	1	1
90°	0	

TEST NUMBER: P1287348

CATALOG NUMBER: P3AS13R709030D2WDE010 E3CB1MMS

CANDELA DISTRIBUTION (FULL):

0°	
0°	1219.8
2.5°	1201.5
5°	1159.5
7.5°	1120.7
10°	1090.6
12.5°	1065.8
15°	1041.1
17.5°	1010.9
20°	975.4
22.5°	934.5
25°	890.4
27.5°	845.1
30°	791.3
32.5°	722.4
35°	628.7
37.5°	509.2
40°	379.0
42.5°	258.4
45°	162.6
47.5°	90.4
50°	38.8
52.5°	12.9
55°	8.6
57.5°	7.5
60°	7.5
62.5°	6.5
65°	5.4
67.5°	5.4
70°	4.3
72.5°	4.3
75°	3.2
77.5°	3.2
80°	2.2
82.5°	2.2
85°	1.1
87.5°	1.1
90°	0.0

(END OF REPORT)