

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1287358

Luminaire Tested: P3AS13R709030D2WDE010 E3DL1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1287358
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-47)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R709030D2WDE010 E3DL1GPH
Description: 3in Adjustable Dim to Warm LED luminaire with, R70 optic, 3000K CCT AND, 90CRI ,
E3DL1GPH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 531.0 lumens
Efficiency: N/A
Efficacy: 26.4 lumens/watt
Spacing Criteria (0/90/45): 0.97 / 0.97 / 0.98
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 20.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1287358

CATALOG NUMBER: P3AS13R709030D2WDE010 E3DL1GPH

Luminous Intensity Polar Plot



TEST NUMBER: P1287358

CATALOG NUMBER: P3AS13R709030D2WDE010 E3DL1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	107	104	110	107	105	103	103	101	100		100	98	97		96
2	106	101	96	93	104	99	95	92	96	93	90		93	90	88		90
3	100	93	88	83	98	92	87	82	89	85	81		86	83	80		84
4	94	86	80	75	93	85	79	75	83	78	74		81	76	73		79
5	89	80	73	69	87	79	73	68	77	72	68		75	71	67		74
6	84	74	68	63	82	73	67	63	72	66	62		70	65	62		69
7	79	69	62	58	78	68	62	58	67	61	57		66	61	57		65
8	75	65	58	53	74	64	58	53	63	57	53		62	57	53		61
9	71	60	54	50	70	60	54	50	59	53	49		58	53	49		57
10	67	57	50	46	66	56	50	46	55	50	46		55	49	46		54

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	102799
5°	101563
10°	98640
15°	94461
20°	88464
25°	80376
30°	69428
35°	55332
40°	40304
45°	26483
50°	12418
55°	3823
60°	3684
65°	3580
70°	3398
75°	3558
80°	3283
85°	2768

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 26483 cd/sqm

TEST NUMBER: P1287358

CATALOG NUMBER: P3AS13R709030D2WDE010 E3DL1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	43.5	8.2
10°-20°	116.4	21.9
20°-30°	151.3	28.5
30°-40°	128.4	24.2
40°-50°	66.2	12.5
50°-60°	12.8	2.4
60°-70°	6.9	1.3
70°-80°	4.2	0.8
80°-90°	1.2	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	311.2	58.6
0°-40°	439.7	82.8
0°-60°	518.6	97.7
0°-90°	531.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	531.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	469	
5°	461	43
15°	416	116
25°	332	151
35°	207	128
45°	85	66
55°	10	13
65°	7	7
75°	4	4
85°	1	1
90°	0	

TEST NUMBER: P1287358

CATALOG NUMBER: P3AS13R709030D2WDE010 E3DL1GPH

CANDELA DISTRIBUTION (FULL):

0°	
0°	468.8
2.5°	467.2
5°	461.4
7.5°	453.0
10°	443.0
12.5°	430.3
15°	416.1
17.5°	398.7
20°	379.1
22.5°	357.0
25°	332.2
27.5°	304.3
30°	274.2
32.5°	241.0
35°	206.7
37.5°	173.0
40°	140.8
42.5°	110.7
45°	85.4
47.5°	62.8
50°	36.4
52.5°	15.8
55°	10.0
57.5°	9.5
60°	8.4
62.5°	7.9
65°	6.9
67.5°	6.3
70°	5.3
72.5°	4.7
75°	4.2
77.5°	3.2
80°	2.6
82.5°	1.6
85°	1.1
87.5°	0.5
90°	0.0

(END OF REPORT)