

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1288619

Luminaire Tested: P3AS05R25W2N902765DE010 E3DLD1GPH_3500K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1288619
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-10)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS05R25W2N902765DE010 E3DLD1GPH_3500K
Description: 3in Adjustable Tunable White LED luminaire with, R25 optic, 3500K CCT AND, 90CRI ,
E3DLD1GPH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 158.0 lumens
Efficiency: N/A
Efficacy: 26.8 lumens/watt
Spacing Criteria (0/90/45): 0.78 / 0.78 / 0.85
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 5.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1288619

CATALOG NUMBER: P3AS05R25W2N902765DE010 E3DLD1GPH_3500K

Luminous Intensity Polar Plot



TEST NUMBER: P1288619

CATALOG NUMBER: P3AS05R25W2N902765DE010 E3DLD1GPH_3500K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10			0
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	112	109	106	104	110	107	104	102	103	101	99		99	98	96		96	94	93	91
2	106	100	96	92	104	99	94	91	95	92	89		92	89	87		89	87	85	83
3	100	92	87	82	98	91	86	82	88	84	80		86	82	79		83	80	78	76
4	94	85	79	74	92	84	78	74	82	77	73		80	76	72		78	74	71	70
5	89	79	73	68	87	78	72	68	76	71	67		75	70	66		73	69	66	64
6	84	74	67	62	82	73	67	62	71	66	62		70	65	61		69	64	61	59
7	79	69	62	58	78	68	62	58	67	61	57		66	61	57		65	60	57	55
8	75	65	58	54	74	64	58	53	63	57	53		62	57	53		61	56	53	51
9	71	61	54	50	70	60	54	50	59	54	50		58	53	50		57	53	49	48
10	68	57	51	47	67	57	51	47	56	50	47		55	50	46		54	50	46	45

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	37541
5°	36650
10°	33956
15°	30261
20°	25996
25°	22090
30°	18180
35°	14161
40°	10191
45°	6481
50°	3821
55°	2638
60°	2412
65°	2231
70°	1988
75°	1864
80°	1768
85°	1510

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 6481 cd/sqm

TEST NUMBER: P1288619

CATALOG NUMBER: P3AS05R25W2N902765DE010 E3DLD1GPH_3500K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	15.4	9.8
10°-20°	37.0	23.4
20°-30°	41.8	26.5
30°-40°	33.1	20.9
40°-50°	16.7	10.6
50°-60°	6.7	4.2
60°-70°	4.3	2.7
70°-80°	2.4	1.5
80°-90°	0.7	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	94.2	59.6
0°-40°	127.3	80.6
0°-60°	150.7	95.4
0°-90°	158.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	158.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	171	
5°	166	15
15°	133	37
25°	91	42
35°	53	33
45°	21	17
55°	7	7
65°	4	4
75°	2	2
85°	1	1
90°	0	

TEST NUMBER: P1288619

CATALOG NUMBER: P3AS05R25W2N902765DE010 E3DLD1GPH_3500K

CANDELA DISTRIBUTION (FULL):

0°	
0°	171.2
1°	171.2
2°	170.7
3°	169.7
4°	168.3
5°	166.5
6°	164.4
7°	161.8
8°	159.0
9°	155.9
10°	152.5
11°	148.8
12°	145.3
13°	141.1
14°	137.2
15°	133.3
17.5°	122.2
20°	111.4
22.5°	101.2
25°	91.3
27.5°	81.7
30°	71.8
32.5°	62.6
35°	52.9
37.5°	44.1
40°	35.6
42.5°	27.8
45°	20.9
47.5°	15.5
50°	11.2
52.5°	8.5
55°	6.9
57.5°	6.3
60°	5.5
62.5°	4.9
65°	4.3
67.5°	3.7
70°	3.1
72.5°	2.8
75°	2.2
77.5°	1.8
80°	1.4
82.5°	1.0
85°	0.6
87.5°	0.2



TEST NUMBER: P1288619

CATALOG NUMBER: P3AS05R25W2N902765DE010 E3DLD1GPH_3500K

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0

(END OF REPORT)