

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1287363

Luminaire Tested: P3AS13R709030D2WDE010 E3DL1WMH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1287363
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-47)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R709030D2WDE010 E3DL1WMH
Description: 3in Adjustable Dim to Warm LED luminaire with, R70 optic, 3000K CCT AND, 90CRI ,
E3DL1WMH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1084.1 lumens
Efficiency: N/A
Efficacy: 53.9 lumens/watt
Spacing Criteria (0/90/45): 0.97 / 0.97 / 0.98
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 20.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1287363
CATALOG NUMBER: P3AS13R709030D2WDE010 E3DL1WMH

Luminous Intensity Polar Plot





TEST NUMBER: P1287363

CATALOG NUMBER: P3AS13R709030D2WDE010 E3DL1WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	113	110	107	104	110	107	105	103	103	101	100	100	98	97	96	95	94	92	92	92	92
2	106	101	96	93	104	99	95	92	96	92	90	93	90	88	90	88	86	84	84	84	84
3	100	93	88	83	98	92	87	82	89	85	81	86	83	80	84	81	79	77	77	77	77
4	94	86	80	75	93	85	79	75	83	78	74	81	76	73	79	75	72	70	70	70	70
5	89	80	73	69	87	79	73	68	77	72	68	75	71	67	74	70	66	65	65	65	65
6	84	74	68	63	82	73	67	63	72	66	62	70	65	62	69	65	61	60	60	60	60
7	79	69	62	58	78	68	62	58	67	61	57	66	61	57	65	60	57	55	55	55	55
8	75	65	58	53	74	64	58	53	63	57	53	62	57	53	61	56	53	51	51	51	51
9	71	60	54	50	70	60	54	50	59	53	49	58	53	49	57	52	49	48	48	48	48
10	67	57	50	46	66	56	50	46	55	50	46	55	49	46	54	49	46	44	44	44	44

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	209852
5°	207329
10°	201355
15°	192827
20°	180616
25°	164090
30°	141743
35°	112966
40°	82268
45°	54083
50°	25347
55°	7837
60°	7543
65°	7264
70°	6924
75°	7286
80°	6819
85°	5535

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 54083 cd/sqm



TEST NUMBER: P1287363

CATALOG NUMBER: P3AS13R709030D2WDE010 E3DL1WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	88.7	8.2
10°-20°	237.7	21.9
20°-30°	308.9	28.5
30°-40°	262.2	24.2
40°-50°	135.2	12.5
50°-60°	26.1	2.4
60°-70°	14.1	1.3
70°-80°	8.7	0.8
80°-90°	2.5	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	635.4	58.6
0°-40°	897.5	82.8
0°-60°	1058.8	97.7
0°-90°	1084.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1084.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	957	
5°	942	89
15°	849	238
25°	678	309
35°	422	262
45°	174	135
55°	20	26
65°	14	14
75°	9	9
85°	2	3
90°	0	



TEST NUMBER: P1287363
CATALOG NUMBER: P3AS13R709030D2WDE010 E3DL1WMH

CANDELA DISTRIBUTION (FULL):

	0°
0°	957.0
2.5°	953.8
5°	941.9
7.5°	924.7
10°	904.3
12.5°	878.4
15°	849.4
17.5°	813.8
20°	774.0
22.5°	728.8
25°	678.2
27.5°	621.1
30°	559.8
32.5°	492.0
35°	422.0
37.5°	353.1
40°	287.4
42.5°	226.1
45°	174.4
47.5°	128.1
50°	74.3
52.5°	32.3
55°	20.5
57.5°	19.4
60°	17.2
62.5°	16.1
65°	14.0
67.5°	12.9
70°	10.8
72.5°	9.7
75°	8.6
77.5°	6.5
80°	5.4
82.5°	3.2
85°	2.2
87.5°	1.1
90°	0.0

(END OF REPORT)