

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1288664

Luminaire Tested: P3AS05R25W2N902765DE010 E3DLP1H_6500K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1288664
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-9)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS05R25W2N902765DE010 E3DLP1H_6500K
Description: 3in Adjustable Tunable White LED luminaire with, R25 optic, 6500K CCT AND, 90CRI ,
E3DLP1H TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 256.1 lumens
Efficiency: N/A
Efficacy: 43.4 lumens/watt
Spacing Criteria (0/90/45): 0.62 / 0.62 / 0.68
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 5.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1288664
CATALOG NUMBER: P3AS05R25W2N902765DE010 E3DLP1H_6500K

Luminous Intensity Polar Plot





TEST NUMBER: P1288664

CATALOG NUMBER: P3AS05R25W2N902765DE010 E3DLP1H_6500K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	113	110	108	105	111	108	106	104	104	102	101	100	99	98	97	96	95	93	93	93	93
2	107	102	98	95	105	101	97	94	97	94	92	94	92	90	92	90	88	86	86	86	86
3	102	95	90	86	100	94	89	86	91	87	84	89	86	83	87	84	82	80	80	80	80
4	97	89	84	79	95	88	83	79	86	81	78	84	80	77	82	79	76	75	75	75	75
5	92	84	78	74	91	83	77	73	81	76	73	79	75	72	78	74	71	70	70	70	70
6	88	79	73	69	86	78	72	68	77	72	68	75	71	67	74	70	67	66	66	66	66
7	84	74	68	64	82	74	68	64	72	67	64	71	67	63	70	66	63	62	62	62	62
8	80	70	65	60	79	70	64	60	69	64	60	68	63	60	67	63	60	58	58	58	58
9	76	67	61	57	75	66	61	57	65	60	57	64	60	57	64	59	56	55	55	55	55
10	73	64	58	54	72	63	58	54	62	57	54	62	57	54	61	57	54	52	52	52	52

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	92931
5°	89170
10°	78110
15°	62793
20°	48234
25°	36510
30°	26384
35°	17534
40°	10620
45°	6202
50°	3957
55°	3211
60°	2807
65°	2491
70°	2052
75°	2033
80°	1515
85°	2013

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 6202 cd/sqm



TEST NUMBER: P1288664

CATALOG NUMBER: P3AS05R25W2N902765DE010 E3DLP1H_6500K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	36.9	14.4
10°-20°	76.5	29.9
20°-30°	69.2	27.0
30°-40°	41.6	16.2
40°-50°	16.5	6.4
50°-60°	7.6	3.0
60°-70°	4.6	1.8
70°-80°	2.5	1.0
80°-90°	0.7	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	182.5	71.3
0°-40°	224.1	87.5
0°-60°	248.2	96.9
0°-90°	256.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	256.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	424	
5°	405	37
15°	277	76
25°	151	69
35°	66	42
45°	20	17
55°	8	8
65°	5	5
75°	2	2
85°	1	1
90°	0	



TEST NUMBER: P1288664
CATALOG NUMBER: P3AS05R25W2N902765DE010 E3DLP1H_6500K

CANDELA DISTRIBUTION (FULL):

0°	
0°	423.8
1°	423.8
2°	421.9
3°	417.5
4°	411.9
5°	405.1
6°	396.3
7°	386.3
8°	374.8
9°	363.2
10°	350.8
11°	336.4
12°	321.7
13°	306.9
14°	292.1
15°	276.6
17.5°	239.9
20°	206.7
22.5°	176.8
25°	150.9
27.5°	126.5
30°	104.2
32.5°	83.8
35°	65.5
37.5°	49.9
40°	37.1
42.5°	27.1
45°	20.0
47.5°	15.2
50°	11.6
52.5°	9.6
55°	8.4
57.5°	7.2
60°	6.4
62.5°	5.2
65°	4.8
67.5°	4.0
70°	3.2
72.5°	2.8
75°	2.4
77.5°	2.0
80°	1.2
82.5°	0.8
85°	0.8
87.5°	0.4



TEST NUMBER: P1288664
CATALOG NUMBER: P3AS05R25W2N902765DE010 E3DLP1H_6500K

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0

(END OF REPORT)