

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1288692

Luminaire Tested: P3AS05R25W2N902765DE010 E3PH1MW\_4000K

Issue Date: 1/29/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1288692  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2509-551-3)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/29/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS05R25W2N902765DE010 E3PH1MW\_4000K  
Description: 3in Adjustable Tunable White LED luminaire with, R25 optic, 4000K CCT AND, 90CRI ,  
E3PH1MW TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 427.0 lumens  
Efficiency: N/A  
Efficacy: 72.4 lumens/watt  
Spacing Criteria (0/90/45): 0.36 / 0.36 / 0.36  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 5.9  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1288692  
CATALOG NUMBER: P3AS05R25W2N902765DE010 E3PH1MW\_4000K

### Luminous Intensity Polar Plot





TEST NUMBER: P1288692

CATALOG NUMBER: P3AS05R25W2N902765DE010 E3PH1MW\_4000K

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	102	102	102	100
1	116	114	112	111	113	112	110	109	108	107	106	104	103	102	101	100	99	99	98	98	98
2	113	109	107	105	111	108	105	103	105	103	101	102	100	99	99	98	97	99	98	97	96
3	110	106	103	100	108	104	102	99	102	100	98	100	98	96	98	96	95	98	96	95	94
4	107	103	99	97	106	102	99	96	100	97	95	98	96	94	96	95	93	96	95	93	92
5	105	100	96	94	103	99	96	93	97	95	93	96	94	92	95	93	91	95	93	91	90
6	102	97	94	91	101	97	93	91	95	93	91	94	92	90	93	91	89	93	91	89	89
7	100	95	92	89	99	95	91	89	94	91	89	93	90	88	92	89	88	92	89	88	87
8	98	93	90	87	98	93	89	87	92	89	87	91	88	87	90	88	86	90	88	86	85
9	97	91	88	86	96	91	88	85	90	87	85	89	87	85	89	86	85	89	86	85	84
10	95	89	86	84	94	89	86	84	88	86	84	88	85	83	87	85	83	87	85	83	83

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	653084
5°	557780
10°	351652
15°	163656
20°	33696
25°	6871
30°	1469
35°	321
40°	172
45°	0
50°	0
55°	0
60°	0
65°	0
70°	0
75°	0
80°	0
85°	0

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 0 cd/sqm



TEST NUMBER: P1288692

CATALOG NUMBER: P3AS05R25W2N902765DE010 E3PH1MW\_4000K

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	211.2	49.5
10°-20°	196.1	45.9
20°-30°	18.5	4.3
30°-40°	1.1	0.3
40°-50°	0.1	0.0
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	425.9	99.7
0°-40°	426.9	100.0
0°-60°	427.0	100.0
0°-90°	427.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	427.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	2978	
5°	2534	211
15°	721	196
25°	28	19
35°	1	1
45°	0	0
55°	0	0
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P1288692  
CATALOG NUMBER: P3AS05R25W2N902765DE010 E3PH1MW\_4000K

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	2978.3
2.5°	2867.5
5°	2534.0
7.5°	2083.3
10°	1579.3
12.5°	1140.8
15°	720.9
17.5°	348.6
20°	144.4
22.5°	57.4
25°	28.4
27.5°	13.3
30°	5.8
32.5°	2.3
35°	1.2
37.5°	0.6
40°	0.6
42.5°	0.0
45°	0.0
47.5°	0.0
50°	0.0
52.5°	0.0
55°	0.0
57.5°	0.0
60°	0.0
62.5°	0.0
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)