

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1287381

Luminaire Tested: P3AS17R159030D2WDE010 E3D1WH

Issue Date: 1/29/2026

**Test Information**

Test Method: LM-79-2019  
Report Number: P1287381  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2501-338-7)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/29/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS17R159030D2WDE010 E3D1WH  
Description: 3in Adjustable Dim to Warm LED luminaire with, R15 optic, 3000K CCT AND, 90CRI , E3D1WH TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 1861.9 lumens  
Efficiency: N/A  
Efficacy: 68.2 lumens/watt  
Spacing Criteria (0/90/45): 0.3 / 0.3 / 0.29  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct

Input Watts (W): 27.3  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1287381

CATALOG NUMBER: P3AS17R159030D2WDE010 E3D1WH

### Luminous Intensity Polar Plot



TEST NUMBER: P1287381

CATALOG NUMBER: P3AS17R159030D2WDE010 E3D1WH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

|     |     |     |     |     |     |     |     |     |     |     |     |  |     |     |     |  |     |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|--|-----|-----|-----|--|-----|
| RF  | 20  |     |     |     | 20  |     |     |     | 20  |     |     |  | 20  |     |     |  | 20  |
| RC  | 80  |     |     |     | 70  |     |     |     | 50  |     |     |  | 30  |     |     |  | 10  |
| RW  | 70  | 50  | 30  | 10  | 70  | 50  | 30  | 10  | 50  | 30  | 10  |  | 50  | 30  | 10  |  | 50  |
| RCR |     |     |     |     |     |     |     |     |     |     |     |  |     |     |     |  |     |
| 0   | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 |  | 106 | 106 | 106 |  | 102 |
| 1   | 116 | 114 | 112 | 111 | 113 | 112 | 110 | 109 | 108 | 107 | 105 |  | 104 | 103 | 102 |  | 101 |
| 2   | 112 | 109 | 107 | 105 | 110 | 108 | 105 | 103 | 105 | 103 | 101 |  | 102 | 100 | 99  |  | 99  |
| 3   | 110 | 106 | 102 | 100 | 108 | 104 | 102 | 99  | 102 | 100 | 98  |  | 100 | 98  | 96  |  | 98  |
| 4   | 107 | 102 | 99  | 96  | 106 | 101 | 98  | 96  | 99  | 97  | 95  |  | 98  | 96  | 94  |  | 96  |
| 5   | 105 | 100 | 96  | 94  | 103 | 99  | 96  | 93  | 97  | 94  | 92  |  | 96  | 93  | 92  |  | 94  |
| 6   | 102 | 97  | 94  | 91  | 101 | 96  | 93  | 91  | 95  | 92  | 90  |  | 94  | 92  | 90  |  | 93  |
| 7   | 100 | 95  | 91  | 89  | 99  | 94  | 91  | 89  | 93  | 90  | 88  |  | 92  | 90  | 88  |  | 91  |
| 8   | 98  | 93  | 89  | 87  | 97  | 92  | 89  | 87  | 91  | 89  | 87  |  | 91  | 88  | 86  |  | 90  |
| 9   | 96  | 91  | 88  | 85  | 96  | 91  | 87  | 85  | 90  | 87  | 85  |  | 89  | 87  | 85  |  | 89  |
| 10  | 95  | 89  | 86  | 84  | 94  | 89  | 86  | 84  | 88  | 85  | 83  |  | 88  | 85  | 83  |  | 87  |

**AVERAGE LUMINANCE (cd/sqm):**

|     |         |
|-----|---------|
|     | 0°      |
| 0°  | 3545725 |
| 5°  | 2891298 |
| 10° | 1415984 |
| 15° | 433396  |
| 20° | 183533  |
| 25° | 83013   |
| 30° | 32359   |
| 35° | 14937   |
| 40° | 4637    |
| 45° | 1737    |
| 50° | 716     |
| 55° | 268     |
| 60° | 307     |
| 65° | 363     |
| 70° | 0       |
| 75° | 0       |
| 80° | 0       |
| 85° | 0       |

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
Vertical Angle: 45°  
Luminance: 1737 cd/sqm

TEST NUMBER: P1287381

CATALOG NUMBER: P3AS17R159030D2WDE010 E3D1WH

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 1022.4 | 54.9      |
| 10°-20°   | 627.4  | 33.7      |
| 20°-30°   | 168.5  | 9.0       |
| 30°-40°   | 37.1   | 2.0       |
| 40°-50°   | 5.2    | 0.3       |
| 50°-60°   | 0.9    | 0.0       |
| 60°-70°   | 0.4    | 0.0       |
| 70°-80°   | 0.0    | 0.0       |
| 80°-90°   | 0.0    | 0.0       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| <hr/>     |        |           |
| 0°-30°    | 1818.3 | 97.7      |
| 0°-40°    | 1855.4 | 99.6      |
| 0°-60°    | 1861.5 | 100.0     |
| 0°-90°    | 1861.9 | 100.0     |
| 90°-120°  | 0.0    | 0.0       |
| 90°-150°  | 0.0    | 0.0       |
| 90°-180°  | 0.0    | 0.0       |
| 0°-180°   | 1861.9 | 100.0     |

**CANDELA DISTRIBUTION:**

|     | 0°    | Flux |
|-----|-------|------|
| 0°  | 16170 |      |
| 5°  | 13135 | ###  |
| 15° | 1909  | 627  |
| 25° | 343   | 169  |
| 35° | 56    | 37   |
| 45° | 6     | 5    |
| 55° | 1     | 1    |
| 65° | 1     | 0    |
| 75° | 0     | 0    |
| 85° | 0     | 0    |
| 90° | 0     |      |

TEST NUMBER: P1287381

CATALOG NUMBER: P3AS17R159030D2WDE010 E3D1WH

**CANDELA DISTRIBUTION (FULL):**

| 0°    |         |
|-------|---------|
| 0°    | 16169.8 |
| 1°    | 16068.9 |
| 2°    | 15744.8 |
| 3°    | 15160.9 |
| 4°    | 14281.9 |
| 5°    | 13135.2 |
| 6°    | 11838.2 |
| 7°    | 10393.7 |
| 8°    | 9066.3  |
| 9°    | 7659.2  |
| 10°   | 6359.3  |
| 11°   | 5072.9  |
| 12°   | 3903.0  |
| 13°   | 3002.1  |
| 14°   | 2376.5  |
| 15°   | 1909.1  |
| 17.5° | 1183.3  |
| 20°   | 786.5   |
| 22.5° | 529.5   |
| 25°   | 343.1   |
| 27.5° | 203.3   |
| 30°   | 127.8   |
| 32.5° | 86.1    |
| 35°   | 55.8    |
| 37.5° | 31.1    |
| 40°   | 16.2    |
| 42.5° | 9.2     |
| 45°   | 5.6     |
| 47.5° | 3.5     |
| 50°   | 2.1     |
| 52.5° | 1.4     |
| 55°   | 0.7     |
| 57.5° | 0.7     |
| 60°   | 0.7     |
| 62.5° | 0.7     |
| 65°   | 0.7     |
| 67.5° | 0.0     |
| 70°   | 0.0     |
| 72.5° | 0.0     |
| 75°   | 0.0     |
| 77.5° | 0.0     |
| 80°   | 0.0     |
| 82.5° | 0.0     |
| 85°   | 0.0     |
| 87.5° | 0.0     |



TEST NUMBER: P1287381

CATALOG NUMBER: P3AS17R159030D2WDE010 E3D1WH

CANDELA DISTRIBUTION (continued):

0°  
90° | 0.0

(END OF REPORT)