

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1288717

Luminaire Tested: P3AS05R30W2N902750DE010 E3CB1MW_2700K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1288717
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-16)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS05R30W2N902750DE010 E3CB1MW_2700K
Description: 3in Adjustable Tunable White LED luminaire with, R30 optic, 2700K CCT AND, 90CRI ,
E3CB1MW TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 456.0 lumens
Efficiency: N/A
Efficacy: 77.3 lumens/watt
Spacing Criteria (0/90/45): 0.53 / 0.53 / 0.47
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 5.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1288717

CATALOG NUMBER: P3AS05R30W2N902750DE010 E3CB1MW_2700K

Luminous Intensity Polar Plot



TEST NUMBER: P1288717

CATALOG NUMBER: P3AS05R30W2N902750DE010 E3CB1MW_2700K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20				20				20
RC	80				70				50				30				10				0				0				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																													
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	99	98	97	96	95	94	93	92	91	90	89
1	115	113	111	109	113	111	109	108	107	106	104	103	102	101	100	99	98	97	96	95	94	93	92	91	90	89	88	87	86
2	111	108	105	102	109	106	104	101	103	101	99	100	99	97	98	96	95	94	93	92	91	90	89	88	87	86	85	84	83
3	108	103	100	97	106	102	99	96	100	97	95	97	95	93	95	94	92	91	90	89	88	87	86	85	84	83	82	81	80
4	105	100	96	93	103	98	95	92	97	94	91	95	92	90	93	91	89	88	87	86	85	84	83	82	81	80	79	78	77
5	102	96	92	89	100	95	91	89	94	90	88	92	89	87	91	88	87	86	85	84	83	82	81	80	79	78	77	76	75
6	99	93	89	86	98	92	88	86	91	88	85	90	87	85	89	86	84	83	82	81	80	79	78	77	76	75	74	73	72
7	96	90	86	83	95	89	86	83	88	85	82	87	84	82	86	84	82	81	80	79	78	77	76	75	74	73	72	71	70
8	94	87	83	81	93	87	83	80	86	83	80	85	82	80	84	82	80	79	78	77	76	75	74	73	72	71	70	69	68
9	91	85	81	78	90	84	81	78	84	80	78	83	80	78	82	79	77	76	75	74	73	72	71	70	69	68	67	66	65
10	89	83	79	76	88	82	78	76	82	78	76	81	78	76	80	77	75	74	73	72	71	70	69	68	67	66	65	64	63

AVERAGE LUMINANCE (cd/sqm):

0°	371330
5°	364318
10°	322506
15°	204337
20°	77567
25°	22961
30°	9065
35°	2784
40°	1231
45°	434
50°	375
55°	268
60°	307
65°	363
70°	256
75°	339
80°	505
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 80°

Luminance: 505 cd/sqm

TEST NUMBER: P1288717

CATALOG NUMBER: P3AS05R30W2N902750DE010 E3CB1MW_2700K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	152.1	33.4
10°-20°	237.1	52.0
20°-30°	55.1	12.1
30°-40°	8.5	1.9
40°-50°	1.5	0.3
50°-60°	0.7	0.1
60°-70°	0.6	0.1
70°-80°	0.4	0.1
80°-90°	0.1	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	444.3	97.4
0°-40°	452.9	99.3
0°-60°	455.0	99.8
0°-90°	456.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	456.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1693	
5°	1655	152
15°	900	237
25°	95	55
35°	10	9
45°	1	1
55°	1	1
65°	1	1
75°	0	0
85°	0	0
90°	0	

TEST NUMBER: P1288717

CATALOG NUMBER: P3AS05R30W2N902750DE010 E3CB1MW_2700K

CANDELA DISTRIBUTION (FULL):

0°	
0°	1693.4
1°	1692.4
2°	1687.7
3°	1679.8
4°	1669.8
5°	1655.1
6°	1636.8
7°	1609.6
8°	1572.4
9°	1517.6
10°	1448.4
11°	1359.3
12°	1258.6
13°	1146.9
14°	1024.0
15°	900.1
17.5°	588.8
20°	332.4
22.5°	169.8
25°	94.9
27.5°	58.4
30°	35.8
32.5°	19.3
35°	10.4
37.5°	6.8
40°	4.3
42.5°	2.5
45°	1.4
47.5°	1.1
50°	1.1
52.5°	0.7
55°	0.7
57.5°	0.7
60°	0.7
62.5°	0.7
65°	0.7
67.5°	0.4
70°	0.4
72.5°	0.4
75°	0.4
77.5°	0.4
80°	0.4
82.5°	0.0
85°	0.0
87.5°	0.0



TEST NUMBER: P1288717

CATALOG NUMBER: P3AS05R30W2N902750DE010 E3CB1MW_2700K

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0

(END OF REPORT)