

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1288786

Luminaire Tested: P3AS05R30W2N902750DE010 E3DL1WH\_5000K

Issue Date: 1/30/2026

**Test Information**

Test Method: LM-79-2019  
Report Number: P1288786  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-13)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS05R30W2N902750DE010 E3DL1WH\_5000K  
Description: 3in Adjustable Tunable White LED luminaire with, R30 optic, 5000K CCT AND, 90CRI ,  
E3DL1WH TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 257.1 lumens  
Efficiency: N/A  
Efficacy: 43.6 lumens/watt  
Spacing Criteria (0/90/45): 0.66 / 0.66 / 0.7  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct

Input Watts (W): 5.9  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1288786

CATALOG NUMBER: P3AS05R30W2N902750DE010 E3DL1WH\_5000K

### Luminous Intensity Polar Plot



TEST NUMBER: P1288786

CATALOG NUMBER: P3AS05R30W2N902750DE010 E3DL1WH\_5000K

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

|     |     |     |     |     |     |     |     |     |     |     |     |  |     |     |     |  |     |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|--|-----|-----|-----|--|-----|
| RF  | 20  |     |     |     | 20  |     |     |     | 20  |     |     |  | 20  |     |     |  | 20  |
| RC  | 80  |     |     |     | 70  |     |     |     | 50  |     |     |  | 30  |     |     |  | 10  |
| RW  | 70  | 50  | 30  | 10  | 70  | 50  | 30  | 10  | 50  | 30  | 10  |  | 50  | 30  | 10  |  | 50  |
| RCR |     |     |     |     |     |     |     |     |     |     |     |  |     |     |     |  |     |
| 0   | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 |  | 106 | 106 | 106 |  | 102 |
| 1   | 113 | 110 | 108 | 105 | 111 | 108 | 106 | 104 | 104 | 102 | 100 |  | 100 | 99  | 97  |  | 97  |
| 2   | 107 | 102 | 98  | 95  | 105 | 101 | 97  | 94  | 97  | 94  | 92  |  | 94  | 92  | 90  |  | 92  |
| 3   | 102 | 95  | 90  | 86  | 100 | 94  | 89  | 85  | 91  | 87  | 84  |  | 89  | 86  | 83  |  | 87  |
| 4   | 97  | 89  | 84  | 79  | 95  | 88  | 83  | 79  | 86  | 81  | 78  |  | 84  | 80  | 77  |  | 82  |
| 5   | 92  | 84  | 78  | 73  | 90  | 83  | 77  | 73  | 81  | 76  | 72  |  | 79  | 75  | 72  |  | 78  |
| 6   | 88  | 79  | 73  | 68  | 86  | 78  | 72  | 68  | 76  | 71  | 68  |  | 75  | 71  | 67  |  | 74  |
| 7   | 83  | 74  | 68  | 64  | 82  | 74  | 68  | 64  | 72  | 67  | 63  |  | 71  | 67  | 63  |  | 70  |
| 8   | 80  | 70  | 64  | 60  | 78  | 70  | 64  | 60  | 69  | 63  | 60  |  | 67  | 63  | 60  |  | 67  |
| 9   | 76  | 67  | 61  | 57  | 75  | 66  | 60  | 57  | 65  | 60  | 56  |  | 64  | 60  | 56  |  | 63  |
| 10  | 73  | 63  | 58  | 54  | 72  | 63  | 57  | 54  | 62  | 57  | 53  |  | 61  | 57  | 53  |  | 60  |

**AVERAGE LUMINANCE (cd/sqm):**

|     |       |
|-----|-------|
|     | 0°    |
| 0°  | 87822 |
| 5°  | 85098 |
| 10° | 76663 |
| 15° | 63428 |
| 20° | 49098 |
| 25° | 36825 |
| 30° | 26738 |
| 35° | 17828 |
| 40° | 10963 |
| 45° | 6419  |
| 50° | 3957  |
| 55° | 3211  |
| 60° | 2807  |
| 65° | 2283  |
| 70° | 2052  |
| 75° | 2033  |
| 80° | 1515  |
| 85° | 2013  |

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
Vertical Angle: 45°  
Luminance: 6419 cd/sqm

TEST NUMBER: P1288786

CATALOG NUMBER: P3AS05R30W2N902750DE010 E3DL1WH\_5000K

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 35.6   | 13.8      |
| 10°-20°   | 76.9   | 29.9      |
| 20°-30°   | 70.0   | 27.2      |
| 30°-40°   | 42.3   | 16.5      |
| 40°-50°   | 17.0   | 6.6       |
| 50°-60°   | 7.5    | 2.9       |
| 60°-70°   | 4.5    | 1.8       |
| 70°-80°   | 2.5    | 1.0       |
| 80°-90°   | 0.7    | 0.3       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| <hr/>     |        |           |
| 0°-30°    | 182.5  | 71.0      |
| 0°-40°    | 224.8  | 87.5      |
| 0°-60°    | 249.3  | 97.0      |
| 0°-90°    | 257.1  | 100.0     |
| 90°-120°  | 0.0    | 0.0       |
| 90°-150°  | 0.0    | 0.0       |
| 90°-180°  | 0.0    | 0.0       |
| 0°-180°   | 257.1  | 100.0     |

**CANDELA DISTRIBUTION:**

|     | 0°  | Flux |
|-----|-----|------|
| 0°  | 400 |      |
| 5°  | 387 | 36   |
| 15° | 279 | 77   |
| 25° | 152 | 70   |
| 35° | 67  | 42   |
| 45° | 21  | 17   |
| 55° | 8   | 8    |
| 65° | 4   | 5    |
| 75° | 2   | 2    |
| 85° | 1   | 1    |
| 90° | 0   |      |

TEST NUMBER: P1288786

CATALOG NUMBER: P3AS05R30W2N902750DE010 E3DL1WH\_5000K

**CANDELA DISTRIBUTION (FULL):**

| 0°    |       |
|-------|-------|
| 0°    | 400.5 |
| 1°    | 400.1 |
| 2°    | 398.5 |
| 3°    | 395.7 |
| 4°    | 391.7 |
| 5°    | 386.6 |
| 6°    | 380.2 |
| 7°    | 373.4 |
| 8°    | 364.6 |
| 9°    | 354.7 |
| 10°   | 344.3 |
| 11°   | 332.4 |
| 12°   | 319.6 |
| 13°   | 306.9 |
| 14°   | 292.9 |
| 15°   | 279.4 |
| 17.5° | 243.9 |
| 20°   | 210.4 |
| 22.5° | 179.3 |
| 25°   | 152.2 |
| 27.5° | 127.5 |
| 30°   | 105.6 |
| 32.5° | 85.3  |
| 35°   | 66.6  |
| 37.5° | 51.0  |
| 40°   | 38.3  |
| 42.5° | 27.9  |
| 45°   | 20.7  |
| 47.5° | 15.5  |
| 50°   | 11.6  |
| 52.5° | 9.2   |
| 55°   | 8.4   |
| 57.5° | 7.2   |
| 60°   | 6.4   |
| 62.5° | 5.2   |
| 65°   | 4.4   |
| 67.5° | 4.0   |
| 70°   | 3.2   |
| 72.5° | 2.8   |
| 75°   | 2.4   |
| 77.5° | 2.0   |
| 80°   | 1.2   |
| 82.5° | 0.8   |
| 85°   | 0.8   |
| 87.5° | 0.4   |



TEST NUMBER: P1288786

CATALOG NUMBER: P3AS05R30W2N902750DE010 E3DL1WH\_5000K

CANDELA DISTRIBUTION (continued):

0°  
90° | 0.0

(END OF REPORT)