

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1288787

Luminaire Tested: P3AS05R30W2N902750DE010 E3DL1WMH\_2700K

Issue Date: 1/30/2026

**Test Information**

Test Method: LM-79-2019  
Report Number: P1288787  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-15)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS05R30W2N902750DE010 E3DL1WMH\_2700K  
Description: 3in Adjustable Tunable White LED luminaire with, R30 optic, 2700K CCT AND, 90CRI ,  
E3DL1WMH TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 380.0 lumens  
Efficiency: N/A  
Efficacy: 64.4 lumens/watt  
Spacing Criteria (0/90/45): 0.54 / 0.54 / 0.54  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct

Input Watts (W): 5.9  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1288787

CATALOG NUMBER: P3AS05R30W2N902750DE010 E3DL1WMH\_2700K

### Luminous Intensity Polar Plot



TEST NUMBER: P1288787

CATALOG NUMBER: P3AS05R30W2N902750DE010 E3DL1WMH\_2700K

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

|     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |    |    |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|----|----|
| RF  | 20  |     |     |     | 20  |     |     |     |     | 20  |     |     |     |     | 20  |     |     |     |    | 20 |
| RC  | 80  |     |     |     | 70  |     |     |     |     | 50  |     |     |     |     | 30  |     |     |     |    | 10 |
| RW  | 70  | 50  | 30  | 10  | 70  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30 | 10 |
| RCR |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |    |    |
| 0   | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 | 106 | 106 | 106 | 102 | 102 | 102 | 100 | 99 | 99 |
| 1   | 114 | 112 | 110 | 108 | 112 | 110 | 108 | 106 | 106 | 104 | 103 | 102 | 101 | 100 | 99  | 98  | 97  | 95  | 94 | 93 |
| 2   | 110 | 105 | 102 | 99  | 107 | 104 | 101 | 98  | 101 | 98  | 96  | 98  | 96  | 94  | 95  | 93  | 92  | 90  | 89 | 88 |
| 3   | 105 | 100 | 96  | 92  | 103 | 98  | 95  | 91  | 96  | 93  | 90  | 94  | 91  | 89  | 91  | 89  | 87  | 86  | 85 | 84 |
| 4   | 101 | 95  | 90  | 87  | 99  | 94  | 89  | 86  | 92  | 88  | 85  | 90  | 87  | 84  | 88  | 85  | 83  | 82  | 81 | 80 |
| 5   | 97  | 90  | 85  | 82  | 96  | 89  | 85  | 81  | 88  | 84  | 81  | 86  | 83  | 80  | 85  | 82  | 79  | 78  | 77 | 76 |
| 6   | 94  | 86  | 81  | 78  | 92  | 85  | 81  | 77  | 84  | 80  | 77  | 83  | 79  | 76  | 81  | 78  | 76  | 75  | 74 | 73 |
| 7   | 90  | 82  | 77  | 74  | 89  | 82  | 77  | 74  | 81  | 76  | 73  | 80  | 76  | 73  | 79  | 75  | 73  | 71  | 70 | 69 |
| 8   | 87  | 79  | 74  | 71  | 86  | 79  | 74  | 71  | 78  | 73  | 70  | 77  | 73  | 70  | 76  | 72  | 70  | 69  | 68 | 67 |
| 9   | 84  | 76  | 71  | 68  | 83  | 75  | 71  | 68  | 75  | 70  | 67  | 74  | 70  | 67  | 73  | 70  | 67  | 66  | 65 | 64 |
| 10  | 81  | 73  | 68  | 65  | 80  | 73  | 68  | 65  | 72  | 68  | 65  | 71  | 67  | 65  | 71  | 67  | 65  | 63  | 62 | 61 |

**AVERAGE LUMINANCE (cd/sqm):**

|     |        |
|-----|--------|
|     | 0°     |
| 0°  | 221737 |
| 5°  | 211049 |
| 10° | 177530 |
| 15° | 128014 |
| 20° | 79410  |
| 25° | 45172  |
| 30° | 25092  |
| 35° | 13652  |
| 40° | 7185   |
| 45° | 3907   |
| 50° | 2081   |
| 55° | 1376   |
| 60° | 1272   |
| 65° | 1297   |
| 70° | 1154   |
| 75° | 932    |
| 80° | 884    |
| 85° | 1006   |

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
Vertical Angle: 45°  
Luminance: 3907 cd/sqm

TEST NUMBER: P1288787

CATALOG NUMBER: P3AS05R30W2N902750DE010 E3DL1WMH\_2700K

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 86.3   | 22.7      |
| 10°-20°   | 153.5  | 40.4      |
| 20°-30°   | 88.7   | 23.3      |
| 30°-40°   | 33.7   | 8.9       |
| 40°-50°   | 10.3   | 2.7       |
| 50°-60°   | 3.5    | 0.9       |
| 60°-70°   | 2.4    | 0.6       |
| 70°-80°   | 1.3    | 0.3       |
| 80°-90°   | 0.4    | 0.1       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| <hr/>     |        |           |
| 0°-30°    | 328.5  | 86.4      |
| 0°-40°    | 362.2  | 95.3      |
| 0°-60°    | 376.0  | 98.9      |
| 0°-90°    | 380.0  | 100.0     |
| 90°-120°  | 0.0    | 0.0       |
| 90°-150°  | 0.0    | 0.0       |
| 90°-180°  | 0.0    | 0.0       |
| 0°-180°   | 380.0  | 100.0     |

**CANDELA DISTRIBUTION:**

|     | 0°   | Flux |
|-----|------|------|
| 0°  | 1011 |      |
| 5°  | 959  | 86   |
| 15° | 564  | 153  |
| 25° | 187  | 89   |
| 35° | 51   | 34   |
| 45° | 13   | 10   |
| 55° | 4    | 3    |
| 65° | 2    | 2    |
| 75° | 1    | 1    |
| 85° | 0    | 0    |
| 90° | 0    |      |

TEST NUMBER: P1288787

CATALOG NUMBER: P3AS05R30W2N902750DE010 E3DL1WMH\_2700K

**CANDELA DISTRIBUTION (FULL):**

| 0°    |        |
|-------|--------|
| 0°    | 1011.2 |
| 1°    | 1010.5 |
| 2°    | 1004.4 |
| 3°    | 992.9  |
| 4°    | 978.6  |
| 5°    | 958.8  |
| 6°    | 933.7  |
| 7°    | 905.7  |
| 8°    | 874.5  |
| 9°    | 837.1  |
| 10°   | 797.3  |
| 11°   | 754.2  |
| 12°   | 708.6  |
| 13°   | 660.9  |
| 14°   | 612.4  |
| 15°   | 563.9  |
| 17.5° | 444.8  |
| 20°   | 340.3  |
| 22.5° | 252.4  |
| 25°   | 186.7  |
| 27.5° | 135.7  |
| 30°   | 99.1   |
| 32.5° | 71.4   |
| 35°   | 51.0   |
| 37.5° | 35.5   |
| 40°   | 25.1   |
| 42.5° | 17.6   |
| 45°   | 12.6   |
| 47.5° | 8.6    |
| 50°   | 6.1    |
| 52.5° | 4.3    |
| 55°   | 3.6    |
| 57.5° | 3.2    |
| 60°   | 2.9    |
| 62.5° | 2.5    |
| 65°   | 2.5    |
| 67.5° | 2.2    |
| 70°   | 1.8    |
| 72.5° | 1.4    |
| 75°   | 1.1    |
| 77.5° | 1.1    |
| 80°   | 0.7    |
| 82.5° | 0.7    |
| 85°   | 0.4    |
| 87.5° | 0.0    |



TEST NUMBER: P1288787

CATALOG NUMBER: P3AS05R30W2N902750DE010 E3DL1WMH\_2700K

CANDELA DISTRIBUTION (continued):

0°  
90° | 0.0

(END OF REPORT)