

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1287427

Luminaire Tested: P3AS17R209030D2WDE010 E3PH1MW

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1287427
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2509-551-2)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS17R209030D2WDE010 E3PH1MW
Description: 3in Adjustable Dim to Warm LED luminaire with, R20 optic, 3000K CCT AND, 90CRI , E3PH1M'
TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1301.0 lumens
Efficiency: N/A
Efficacy: 47.7 lumens/watt
Spacing Criteria (0/90/45): 0.32 / 0.32 / 0.32
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 27.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1287427

CATALOG NUMBER: P3AS17R209030D2WDE010 E3PH1MW

Luminous Intensity Polar Plot



TEST NUMBER: P1287427

CATALOG NUMBER: P3AS17R209030D2WDE010 E3PH1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	116	114	112	111	113	112	110	109	108	107	106		104	104	103		101
2	113	110	107	105	111	108	106	104	105	104	102		102	101	100		100
3	110	107	104	101	109	105	103	101	103	101	99		101	99	98		99
4	108	104	101	98	107	103	100	98	101	98	97		99	97	95		97
5	106	101	98	96	105	100	97	95	99	96	94		97	95	94		96
6	104	99	96	93	103	98	95	93	97	94	93		96	94	92		95
7	102	97	94	92	101	96	93	91	95	93	91		95	92	90		94
8	100	95	92	90	99	95	92	90	94	91	89		93	91	89		92
9	99	94	90	88	98	93	90	88	92	90	88		92	89	88		91
10	97	92	89	87	96	92	89	87	91	88	87		91	88	87		90

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	2587051
5°	1987052
10°	1224159
15°	356256
20°	47534
25°	14081
30°	4203
35°	562
40°	601
45°	0
50°	0
55°	0
60°	0
65°	0
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 0 cd/sqm

TEST NUMBER: P1287427

CATALOG NUMBER: P3AS17R209030D2WDE010 E3PH1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	751.8	57.8
10°-20°	512.8	39.4
20°-30°	33.0	2.5
30°-40°	3.3	0.3
40°-50°	0.2	0.0
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1297.6	99.7
0°-40°	1300.8	100.0
0°-60°	1301.0	100.0
0°-90°	1301.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1301.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	11798	
5°	9027	752
15°	1569	513
25°	58	33
35°	2	3
45°	0	0
55°	0	0
65°	0	0
75°	0	0
85°	0	0
90°	0	

TEST NUMBER: P1287427

CATALOG NUMBER: P3AS17R209030D2WDE010 E3PH1MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	11797.9
2.5°	10638.1
5°	9027.2
7.5°	7241.7
10°	5497.8
12.5°	3448.3
15°	1569.3
17.5°	496.8
20°	203.7
22.5°	108.1
25°	58.2
27.5°	29.1
30°	16.6
32.5°	8.3
35°	2.1
37.5°	2.1
40°	2.1
42.5°	0.0
45°	0.0
47.5°	0.0
50°	0.0
52.5°	0.0
55°	0.0
57.5°	0.0
60°	0.0
62.5°	0.0
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)