

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1287431

Luminaire Tested: P3AS17R259030D2WDE010 E3CB1MMS

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1287431
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-12)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS17R259030D2WDE010 E3CB1MMS
Description: 3in Adjustable Dim to Warm LED luminaire with, R25 optic, 3000K CCT AND, 90CRI ,
E3CB1MMS TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1833.0 lumens
Efficiency: N/A
Efficacy: 67.1 lumens/watt
Spacing Criteria (0/90/45): 0.45 / 0.45 / 0.41
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 27.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1287431
CATALOG NUMBER: P3AS17R259030D2WDE010 E3CB1MMS

Luminous Intensity Polar Plot





TEST NUMBER: P1287431
 CATALOG NUMBER: P3AS17R259030D2WDE010 E3CB1MMS

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	99	99	100
1	115	113	111	110	113	111	109	108	107	106	105	103	103	102	100	99	99	97	97	97	97
2	112	108	105	103	110	107	104	102	104	102	100	101	99	98	98	97	96	94	94	94	94
3	108	104	101	98	107	103	100	97	100	98	96	98	96	94	96	94	93	92	92	92	92
4	105	100	97	94	104	99	96	93	97	95	92	96	93	91	94	92	90	89	89	89	89
5	103	97	93	90	101	96	93	90	95	92	89	93	91	89	92	90	88	87	87	87	87
6	100	94	90	87	99	93	90	87	92	89	87	91	88	86	90	87	86	85	85	85	85
7	97	91	88	85	96	91	87	85	90	87	84	89	86	84	88	85	83	83	83	83	83
8	95	89	85	83	94	89	85	82	88	84	82	87	84	82	86	83	81	81	81	81	81
9	93	87	83	80	92	86	83	80	86	82	80	85	82	80	84	82	80	79	79	79	79
10	91	85	81	78	90	84	81	78	84	80	78	83	80	78	82	80	78	77	77	77	77

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1959733
5°	1817605
10°	1409593
15°	706815
20°	232210
25°	92328
30°	34638
35°	10012
40°	4523
45°	1799
50°	1467
55°	1109
60°	1272
65°	1505
70°	898
75°	1186
80°	1768
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 1799 cd/sqm



TEST NUMBER: P1287431

CATALOG NUMBER: P3AS17R259030D2WDE010 E3CB1MMS

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	726.3	39.6
10°-20°	866.5	47.3
20°-30°	195.3	10.7
30°-40°	31.7	1.7
40°-50°	5.7	0.3
50°-60°	3.1	0.2
60°-70°	2.7	0.1
70°-80°	1.5	0.1
80°-90°	0.2	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1788.2	97.6
0°-40°	1819.8	99.3
0°-60°	1828.6	99.8
0°-90°	1833.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1833.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	8937	
5°	8257	726
15°	3114	867
25°	382	195
35°	37	32
45°	6	6
55°	3	3
65°	3	3
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P1287431
CATALOG NUMBER: P3AS17R259030D2WDE010 E3CB1MMS

CANDELA DISTRIBUTION (FULL):

0°	
0°	8937.1
1°	8922.7
2°	8850.7
3°	8718.3
4°	8518.1
5°	8257.4
6°	7946.4
7°	7609.4
8°	7223.4
9°	6801.5
10°	6330.6
11°	5787.7
12°	5162.7
13°	4508.9
14°	3807.6
15°	3113.5
17.5°	1774.2
20°	995.1
22.5°	600.5
25°	381.6
27.5°	234.7
30°	136.8
32.5°	72.0
35°	37.4
37.5°	24.5
40°	15.8
42.5°	10.1
45°	5.8
47.5°	4.3
50°	4.3
52.5°	4.3
55°	2.9
57.5°	2.9
60°	2.9
62.5°	2.9
65°	2.9
67.5°	2.9
70°	1.4
72.5°	1.4
75°	1.4
77.5°	1.4
80°	1.4
82.5°	0.0
85°	0.0
87.5°	0.0



TEST NUMBER: P1287431
CATALOG NUMBER: P3AS17R259030D2WDE010 E3CB1MMS

CANDELA DISTRIBUTION (continued):

90° | $\frac{0^\circ}{0.0}$

(END OF REPORT)