

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1288823

Luminaire Tested: P3AS05R30W2N902750DE010 E3DLP1GPH_3000K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1288823
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-13)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS05R30W2N902750DE010 E3DLP1GPH_3000K
Description: 3in Adjustable Tunable White LED luminaire with, R30 optic, 3000K CCT AND, 90CRI ,
E3DLP1GPH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 125.1 lumens
Efficiency: N/A
Efficacy: 21.2 lumens/watt
Spacing Criteria (0/90/45): 0.66 / 0.66 / 0.7
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 5.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1288823

CATALOG NUMBER: P3AS05R30W2N902750DE010 E3DLP1GPH_3000K

Luminous Intensity Polar Plot



TEST NUMBER: P1288823

CATALOG NUMBER: P3AS05R30W2N902750DE010 E3DLP1GPH_3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10			0
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	113	110	108	105	111	108	106	104	104	102	100		100	99	97		97	96	95	93
2	107	102	98	95	105	101	97	94	97	94	92		94	92	90		92	90	88	86
3	102	95	90	86	100	94	89	85	91	87	84		89	86	83		87	84	81	80
4	97	89	83	79	95	88	83	79	86	81	78		84	80	77		82	79	76	74
5	92	84	78	73	90	83	77	73	81	76	72		79	75	72		78	74	71	70
6	88	79	73	68	86	78	72	68	76	71	68		75	71	67		74	70	67	65
7	83	74	68	64	82	74	68	64	72	67	63		71	66	63		70	66	63	61
8	80	70	64	60	78	70	64	60	68	63	60		67	63	60		67	62	59	58
9	76	67	61	57	75	66	60	57	65	60	56		64	60	56		63	59	56	55
10	73	63	58	54	72	63	57	54	62	57	53		61	57	53		60	56	53	52

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	42716
5°	41382
10°	37296
15°	30851
20°	23872
25°	17904
30°	13015
35°	8673
40°	5324
45°	3132
50°	1910
55°	1567
60°	1360
65°	1090
70°	1026
75°	1017
80°	758
85°	1006

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 3132 cd/sqm

TEST NUMBER: P1288823

CATALOG NUMBER: P3AS05R30W2N902750DE010 E3DLP1GPH_3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	17.3	13.8
10°-20°	37.4	29.9
20°-30°	34.0	27.2
30°-40°	20.6	16.5
40°-50°	8.3	6.6
50°-60°	3.7	2.9
60°-70°	2.2	1.7
70°-80°	1.2	1.0
80°-90°	0.4	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	88.7	71.0
0°-40°	109.3	87.4
0°-60°	121.3	97.0
0°-90°	125.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	125.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	195	
5°	188	17
15°	136	37
25°	74	34
35°	32	21
45°	10	8
55°	4	4
65°	2	2
75°	1	1
85°	0	0
90°	0	

TEST NUMBER: P1288823

CATALOG NUMBER: P3AS05R30W2N902750DE010 E3DLP1GPH_3000K

CANDELA DISTRIBUTION (FULL):

0°	
0°	194.8
1°	194.6
2°	193.8
3°	192.5
4°	190.5
5°	188.0
6°	184.9
7°	181.6
8°	177.4
9°	172.5
10°	167.5
11°	161.7
12°	155.4
13°	149.2
14°	142.5
15°	135.9
17.5°	118.6
20°	102.3
22.5°	87.2
25°	74.0
27.5°	62.0
30°	51.4
32.5°	41.5
35°	32.4
37.5°	24.8
40°	18.6
42.5°	13.6
45°	10.1
47.5°	7.6
50°	5.6
52.5°	4.5
55°	4.1
57.5°	3.5
60°	3.1
62.5°	2.5
65°	2.1
67.5°	1.9
70°	1.6
72.5°	1.4
75°	1.2
77.5°	1.0
80°	0.6
82.5°	0.4
85°	0.4
87.5°	0.2



TEST NUMBER: P1288823

CATALOG NUMBER: P3AS05R30W2N902750DE010 E3DLP1GPH_3000K

CANDELA DISTRIBUTION (continued):



(END OF REPORT)