

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1289010

Luminaire Tested: P3AS05R30W2N902765DE010 E3DLP1GPH_6500K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1289010
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-13)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS05R30W2N902765DE010 E3DLP1GPH_6500K
Description: 3in Adjustable Tunable White LED luminaire with, R30 optic, 6500K CCT AND, 90CRI ,
E3DLP1GPH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 126.0 lumens
Efficiency: N/A
Efficacy: 21.4 lumens/watt
Spacing Criteria (0/90/45): 0.66 / 0.66 / 0.7
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 5.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1289010
CATALOG NUMBER: P3AS05R30W2N902765DE010 E3DLP1GPH_6500K

Luminous Intensity Polar Plot





TEST NUMBER: P1289010
 CATALOG NUMBER: P3AS05R30W2N902765DE010 E3DLP1GPH_6500K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	113	110	108	105	111	108	106	104	104	102	100	100	99	97	97	96	95	93			93
2	107	102	98	95	105	101	97	94	97	94	92	94	92	90	92	90	88	86			86
3	102	95	90	86	100	94	89	85	91	87	84	89	86	83	87	84	81	80			80
4	97	89	83	79	95	88	83	79	86	81	78	84	80	77	82	79	76	74			74
5	92	84	78	73	90	83	77	73	81	76	72	79	75	72	78	74	71	70			70
6	88	79	73	68	86	78	72	68	76	71	68	75	71	67	74	70	67	65			65
7	83	74	68	64	82	74	68	64	72	67	63	71	67	63	70	66	63	61			61
8	80	70	64	60	78	70	64	60	69	63	60	67	63	60	67	62	59	58			58
9	76	67	61	57	75	66	60	57	65	60	56	64	60	56	63	59	56	55			55
10	73	63	58	54	72	63	57	54	62	57	53	61	57	53	60	56	53	52			52

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	43067
5°	41712
10°	37586
15°	31101
20°	24082
25°	18049
30°	13116
35°	8727
40°	5382
45°	3163
50°	1944
55°	1567
60°	1360
65°	1090
70°	1026
75°	1017
80°	758
85°	1006

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 3163 cd/sqm



TEST NUMBER: P1289010
 CATALOG NUMBER: P3AS05R30W2N902765DE010 E3DLP1GPH_6500K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	17.4	13.8
10°-20°	37.7	29.9
20°-30°	34.3	27.2
30°-40°	20.7	16.5
40°-50°	8.3	6.6
50°-60°	3.7	2.9
60°-70°	2.2	1.8
70°-80°	1.2	1.0
80°-90°	0.4	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	89.5	71.0
0°-40°	110.2	87.4
0°-60°	122.2	97.0
0°-90°	126.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	126.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	196	
5°	190	17
15°	137	38
25°	75	34
35°	33	21
45°	10	8
55°	4	4
65°	2	2
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P1289010
CATALOG NUMBER: P3AS05R30W2N902765DE010 E3DLP1GPH_6500K

CANDELA DISTRIBUTION (FULL):

0°	
0°	196.4
1°	196.2
2°	195.4
3°	194.0
4°	192.1
5°	189.5
6°	186.4
7°	183.1
8°	178.8
9°	173.9
10°	168.8
11°	162.9
12°	156.7
13°	150.4
14°	143.6
15°	137.0
17.5°	119.6
20°	103.2
22.5°	87.9
25°	74.6
27.5°	62.5
30°	51.8
32.5°	41.8
35°	32.6
37.5°	25.0
40°	18.8
42.5°	13.7
45°	10.2
47.5°	7.6
50°	5.7
52.5°	4.5
55°	4.1
57.5°	3.5
60°	3.1
62.5°	2.5
65°	2.1
67.5°	2.0
70°	1.6
72.5°	1.4
75°	1.2
77.5°	1.0
80°	0.6
82.5°	0.4
85°	0.4
87.5°	0.2



TEST NUMBER: P1289010
CATALOG NUMBER: P3AS05R30W2N902765DE010 E3DLP1GPH_6500K

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0

(END OF REPORT)