

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1289018

Luminaire Tested: P3AS05R30W2N902765DE010 E3DLP1LI\_3000K

Issue Date: 1/30/2026

**Test Information**

Test Method: LM-79-2019  
Report Number: P1289018  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-13)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS05R30W2N902765DE010 E3DLP1LI\_3000K  
Description: 3in Adjustable Tunable White LED luminaire with, R30 optic, 3000K CCT AND, 90CRI ,  
E3DLP1LI TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 255.0 lumens  
Efficiency: N/A  
Efficacy: 43.2 lumens/watt  
Spacing Criteria (0/90/45): 0.66 / 0.66 / 0.7  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct

Input Watts (W): 5.9  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1289018

CATALOG NUMBER: P3AS05R30W2N902765DE010 E3DLP1LI\_3000K

### Luminous Intensity Polar Plot



TEST NUMBER: P1289018

CATALOG NUMBER: P3AS05R30W2N902765DE010 E3DLP1LI\_3000K

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

|     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |    |    |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|----|----|
| RF  | 20  |     |     |     | 20  |     |     |     |     | 20  |     |     |     |     | 20  |     |     |     |    | 20 |
| RC  | 80  |     |     |     | 70  |     |     |     |     | 50  |     |     |     |     | 30  |     |     |     |    | 10 |
| RW  | 70  | 50  | 30  | 10  | 70  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30 | 10 |
| RCR |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |    |    |
| 0   | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 | 106 | 106 | 106 | 102 | 102 | 102 | 100 |    |    |
| 1   | 113 | 110 | 108 | 105 | 111 | 108 | 106 | 104 | 104 | 102 | 100 | 100 | 99  | 97  | 97  | 96  | 95  | 93  |    |    |
| 2   | 107 | 102 | 98  | 95  | 105 | 101 | 97  | 94  | 97  | 94  | 92  | 94  | 92  | 90  | 92  | 90  | 88  | 86  |    |    |
| 3   | 102 | 95  | 90  | 86  | 100 | 94  | 89  | 85  | 91  | 87  | 84  | 89  | 86  | 83  | 87  | 84  | 82  | 80  |    |    |
| 4   | 97  | 89  | 84  | 79  | 95  | 88  | 83  | 79  | 86  | 81  | 78  | 84  | 80  | 77  | 82  | 79  | 76  | 74  |    |    |
| 5   | 92  | 84  | 78  | 73  | 90  | 83  | 77  | 73  | 81  | 76  | 72  | 79  | 75  | 72  | 78  | 74  | 71  | 70  |    |    |
| 6   | 88  | 79  | 73  | 68  | 86  | 78  | 72  | 68  | 76  | 71  | 68  | 75  | 71  | 67  | 74  | 70  | 67  | 65  |    |    |
| 7   | 83  | 74  | 68  | 64  | 82  | 74  | 68  | 64  | 72  | 67  | 63  | 71  | 67  | 63  | 70  | 66  | 63  | 61  |    |    |
| 8   | 80  | 70  | 64  | 60  | 78  | 70  | 64  | 60  | 69  | 63  | 60  | 67  | 63  | 60  | 67  | 62  | 59  | 58  |    |    |
| 9   | 76  | 67  | 61  | 57  | 75  | 66  | 60  | 57  | 65  | 60  | 56  | 64  | 60  | 56  | 63  | 59  | 56  | 55  |    |    |
| 10  | 73  | 63  | 58  | 54  | 72  | 63  | 57  | 54  | 62  | 57  | 53  | 61  | 57  | 53  | 60  | 56  | 53  | 52  |    |    |

**AVERAGE LUMINANCE (cd/sqm):**

|     |       |
|-----|-------|
|     | 0°    |
| 0°  | 87142 |
| 5°  | 84415 |
| 10° | 76062 |
| 15° | 62929 |
| 20° | 48724 |
| 25° | 36534 |
| 30° | 26536 |
| 35° | 17668 |
| 40° | 10878 |
| 45° | 6388  |
| 50° | 3923  |
| 55° | 3173  |
| 60° | 2763  |
| 65° | 2231  |
| 70° | 2052  |
| 75° | 2033  |
| 80° | 1515  |
| 85° | 2013  |

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
Vertical Angle: 45°  
Luminance: 6388 cd/sqm

TEST NUMBER: P1289018

CATALOG NUMBER: P3AS05R30W2N902765DE010 E3DLP1LI\_3000K

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 35.3   | 13.8      |
| 10°-20°   | 76.3   | 29.9      |
| 20°-30°   | 69.4   | 27.2      |
| 30°-40°   | 42.0   | 16.5      |
| 40°-50°   | 16.9   | 6.6       |
| 50°-60°   | 7.5    | 2.9       |
| 60°-70°   | 4.5    | 1.8       |
| 70°-80°   | 2.5    | 1.0       |
| 80°-90°   | 0.7    | 0.3       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| <hr/>     |        |           |
| 0°-30°    | 181.1  | 71.0      |
| 0°-40°    | 223.1  | 87.5      |
| 0°-60°    | 247.4  | 97.0      |
| 0°-90°    | 255.0  | 100.0     |
| 90°-120°  | 0.0    | 0.0       |
| 90°-150°  | 0.0    | 0.0       |
| 90°-180°  | 0.0    | 0.0       |
| 0°-180°   | 255.0  | 100.0     |

**CANDELA DISTRIBUTION:**

|     | 0°  | Flux |
|-----|-----|------|
| 0°  | 397 |      |
| 5°  | 384 | 35   |
| 15° | 277 | 76   |
| 25° | 151 | 69   |
| 35° | 66  | 42   |
| 45° | 21  | 17   |
| 55° | 8   | 7    |
| 65° | 4   | 4    |
| 75° | 2   | 2    |
| 85° | 1   | 1    |
| 90° | 0   |      |

TEST NUMBER: P1289018

CATALOG NUMBER: P3AS05R30W2N902765DE010 E3DLP1LI\_3000K

**CANDELA DISTRIBUTION (FULL):**

| 0°    |       |
|-------|-------|
| 0°    | 397.4 |
| 1°    | 397.0 |
| 2°    | 395.4 |
| 3°    | 392.6 |
| 4°    | 388.7 |
| 5°    | 383.5 |
| 6°    | 377.2 |
| 7°    | 370.5 |
| 8°    | 361.8 |
| 9°    | 351.9 |
| 10°   | 341.6 |
| 11°   | 329.8 |
| 12°   | 317.1 |
| 13°   | 304.5 |
| 14°   | 290.6 |
| 15°   | 277.2 |
| 17.5° | 242.0 |
| 20°   | 208.8 |
| 22.5° | 177.9 |
| 25°   | 151.0 |
| 27.5° | 126.5 |
| 30°   | 104.8 |
| 32.5° | 84.6  |
| 35°   | 66.0  |
| 37.5° | 50.6  |
| 40°   | 38.0  |
| 42.5° | 27.7  |
| 45°   | 20.6  |
| 47.5° | 15.4  |
| 50°   | 11.5  |
| 52.5° | 9.1   |
| 55°   | 8.3   |
| 57.5° | 7.1   |
| 60°   | 6.3   |
| 62.5° | 5.1   |
| 65°   | 4.3   |
| 67.5° | 4.0   |
| 70°   | 3.2   |
| 72.5° | 2.8   |
| 75°   | 2.4   |
| 77.5° | 2.0   |
| 80°   | 1.2   |
| 82.5° | 0.8   |
| 85°   | 0.8   |
| 87.5° | 0.4   |



TEST NUMBER: P1289018

CATALOG NUMBER: P3AS05R30W2N902765DE010 E3DLP1LI\_3000K

**CANDELA DISTRIBUTION (continued):**

0°  
90° | 0.0

(END OF REPORT)