

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1287469

Luminaire Tested: P3AS17R309030D2WDE010 E3D1LI

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1287469
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2501-338-10)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS17R309030D2WDE010 E3D1LI
Description: 3in Adjustable Dim to Warm LED luminaire with, R30 optic, 3000K CCT AND, 90CRI , E3D1LI TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1818.0 lumens
Efficiency: N/A
Efficacy: 66.6 lumens/watt
Spacing Criteria (0/90/45): 0.52 / 0.52 / 0.47
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 27.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1287469

CATALOG NUMBER: P3AS17R309030D2WDE010 E3D1LI

Luminous Intensity Polar Plot



TEST NUMBER: P1287469

CATALOG NUMBER: P3AS17R309030D2WDE010 E3D1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111		106	106	106		102	102	102
1	115	113	111	109		113	111	109	108		107	106	104		103	102	101		100	99	98
2	111	108	105	102		109	106	103	101		103	101	99		100	98	97		97	96	95
3	108	103	100	97		106	102	99	96		99	97	95		97	95	93		95	93	92
4	105	99	95	92		103	98	95	92		96	93	91		94	92	90		93	91	89
5	101	96	92	89		100	95	91	88		93	90	87		92	89	87		90	88	86
6	99	92	88	85		97	92	88	85		90	87	85		89	86	84		88	85	83
7	96	89	85	82		95	89	85	82		88	84	82		87	84	81		86	83	81
8	93	87	83	80		92	86	82	80		85	82	79		84	81	79		84	81	79
9	91	84	80	77		90	84	80	77		83	79	77		82	79	77		82	79	77
10	88	82	78	75		88	81	78	75		81	77	75		80	77	75		80	77	75

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1446463
5°	1427599
10°	1246425
15°	792241
20°	313884
25°	104837
30°	48792
35°	22111
40°	8473
45°	4155
50°	1194
55°	535
60°	307
65°	363
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 4155 cd/sqm

TEST NUMBER: P1287469

CATALOG NUMBER: P3AS17R309030D2WDE010 E3D1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	593.0	32.6
10°-20°	919.5	50.6
20°-30°	237.1	13.0
30°-40°	55.7	3.1
40°-50°	10.9	0.6
50°-60°	1.2	0.1
60°-70°	0.6	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1749.6	96.2
0°-40°	1805.3	99.3
0°-60°	1817.4	100.0
0°-90°	1818.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1818.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	6596	
5°	6486	593
15°	3490	920
25°	433	237
35°	83	56
45°	13	11
55°	1	1
65°	1	1
75°	0	0
85°	0	0
90°	0	

TEST NUMBER: P1287469

CATALOG NUMBER: P3AS17R309030D2WDE010 E3D1LI

CANDELA DISTRIBUTION (FULL):

0°	
0°	6596.4
1°	6591.4
2°	6575.9
3°	6558.3
4°	6532.1
5°	6485.6
6°	6410.1
7°	6284.4
8°	6113.0
9°	5889.2
10°	5597.8
11°	5251.3
12°	4873.0
13°	4437.6
14°	3981.7
15°	3489.8
16°	3007.8
17°	2543.4
18°	2098.1
19°	1689.5
20°	1345.1
21°	1058.6
22°	832.8
23°	659.1
24°	527.9
25°	433.3
26°	361.3
27°	307.0
28°	265.4
29°	227.2
30°	192.7
32.5°	121.4
35°	82.6
37.5°	51.5
40°	29.6
42.5°	19.8
45°	13.4
47.5°	7.8
50°	3.5
52.5°	1.4
55°	1.4
57.5°	0.7
60°	0.7
62.5°	0.7
65°	0.7



TEST NUMBER: P1287469

CATALOG NUMBER: P3AS17R309030D2WDE010 E3D1LI

CANDELA DISTRIBUTION (continued):

	0°
67.5°	0.7
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)