

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1287491

Luminaire Tested: P3AS17R309030D2WDE010 E3PH1MW

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1287491
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2509-551-4)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS17R309030D2WDE010 E3PH1MW
Description: 3in Adjustable Dim to Warm LED luminaire with, R30 optic, 3000K CCT AND, 90CRI , E3PH1M'
TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1484.0 lumens
Efficiency: N/A
Efficacy: 54.4 lumens/watt
Spacing Criteria (0/90/45): 0.33 / 0.33 / 0.34
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 27.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1287491

CATALOG NUMBER: P3AS17R309030D2WDE010 E3PH1MW

Luminous Intensity Polar Plot



TEST NUMBER: P1287491

CATALOG NUMBER: P3AS17R309030D2WDE010 E3PH1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	115	113	112	110	113	111	110	108	107	106	105		104	103	102		100
2	112	109	106	104	110	107	105	103	104	102	100		101	100	98		99
3	109	105	102	99	107	104	101	98	101	99	97		99	97	95		97
4	106	101	98	95	105	100	97	95	98	96	94		97	94	92		95
5	104	98	95	92	102	97	94	91	96	93	91		94	92	90		93
6	101	95	92	89	100	95	91	89	94	91	88		92	90	88		91
7	99	93	89	87	98	92	89	86	91	88	86		90	88	86		89
8	96	91	87	84	96	90	87	84	89	86	84		88	86	84		88
9	94	89	85	82	94	88	85	82	87	84	82		87	84	82		86
10	92	87	83	81	92	86	83	81	86	82	80		85	82	80		84

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	2112265
5°	1845120
10°	1012206
15°	465701
20°	250995
25°	85069
30°	11065
35°	1660
40°	601
45°	0
50°	0
55°	0
60°	0
65°	0
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 0 cd/sqm

TEST NUMBER: P1287491

CATALOG NUMBER: P3AS17R309030D2WDE010 E3PH1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	671.5	45.3
10°-20°	615.5	41.5
20°-30°	189.3	12.8
30°-40°	7.1	0.5
40°-50°	0.6	0.0
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1476.3	99.5
0°-40°	1483.4	100.0
0°-60°	1484.0	100.0
0°-90°	1484.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1484.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	9633	
5°	8382	672
15°	2051	615
25°	352	189
35°	6	7
45°	0	1
55°	0	0
65°	0	0
75°	0	0
85°	0	0
90°	0	

TEST NUMBER: P1287491

CATALOG NUMBER: P3AS17R309030D2WDE010 E3PH1MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	9632.7
2.5°	9408.0
5°	8382.4
7.5°	6576.5
10°	4545.9
12.5°	3077.1
15°	2051.4
17.5°	1437.6
20°	1075.6
22.5°	724.0
25°	351.6
27.5°	129.0
30°	43.7
32.5°	14.6
35°	6.2
37.5°	4.2
40°	2.1
42.5°	2.1
45°	0.0
47.5°	0.0
50°	0.0
52.5°	0.0
55°	0.0
57.5°	0.0
60°	0.0
62.5°	0.0
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)