

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1287513

Luminaire Tested: P3AS17R359030D2WDE010 E3DLP1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1287513
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-17)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS17R359030D2WDE010 E3DLP1GPH
Description: 3in Adjustable Dim to Warm LED luminaire with, R35 optic, 3000K CCT AND, 90CRI ,
E3DLP1GPH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 458.0 lumens
Efficiency: N/A
Efficacy: 16.8 lumens/watt
Spacing Criteria (0/90/45): 0.69 / 0.69 / 0.72
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 27.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1287513

CATALOG NUMBER: P3AS17R359030D2WDE010 E3DLP1GPH

Luminous Intensity Polar Plot



TEST NUMBER: P1287513

CATALOG NUMBER: P3AS17R359030D2WDE010 E3DLP1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	108	105	111	108	106	104	104	102	100		100	99	97		97
2	107	102	98	94	105	100	97	93	97	94	91		94	92	89		91
3	102	95	90	86	100	94	89	85	91	87	84		89	85	82		86
4	97	89	83	79	95	88	82	78	86	81	77		84	80	77		82
5	92	83	77	73	90	82	77	73	81	76	72		79	75	71		77
6	87	78	72	68	86	77	72	68	76	71	67		75	70	67		73
7	83	74	68	63	82	73	67	63	72	67	63		71	66	63		69
8	79	70	64	60	78	69	63	59	68	63	59		67	62	59		66
9	76	66	60	56	75	66	60	56	65	59	56		64	59	56		63
10	72	63	57	53	71	62	57	53	61	56	53		61	56	53		60

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	147203
5°	143583
10°	131260
15°	111419
20°	88208
25°	66705
30°	48564
35°	32846
40°	20181
45°	11598
50°	6993
55°	5658
60°	4956
65°	4410
70°	3590
75°	3558
80°	3536
85°	3522

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 11598 cd/sqm

TEST NUMBER: P1287513

CATALOG NUMBER: P3AS17R359030D2WDE010 E3DLP1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	60.3	13.2
10°-20°	135.3	29.5
20°-30°	126.6	27.6
30°-40°	77.5	16.9
40°-50°	30.6	6.7
50°-60°	13.4	2.9
60°-70°	8.4	1.8
70°-80°	4.4	1.0
80°-90°	1.5	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	322.2	70.3
0°-40°	399.6	87.3
0°-60°	443.6	96.9
0°-90°	458.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	458.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	671	
5°	652	60
15°	491	135
25°	276	127
35°	123	77
45°	37	31
55°	15	13
65°	8	8
75°	4	4
85°	1	2
90°	0	

TEST NUMBER: P1287513

CATALOG NUMBER: P3AS17R359030D2WDE010 E3DLP1GPH

CANDELA DISTRIBUTION (FULL):


0°	
0°	671.3
1°	672.1
2°	669.9
3°	665.7
4°	659.4
5°	652.3
6°	643.1
7°	632.6
8°	619.9
9°	605.8
10°	589.5
11°	572.6
12°	554.3
13°	534.5
14°	512.7
15°	490.8
17.5°	434.4
20°	378.0
22.5°	323.7
25°	275.7
27.5°	231.3
30°	191.8
32.5°	155.1
35°	122.7
37.5°	93.8
40°	70.5
42.5°	50.8
45°	37.4
47.5°	26.8
50°	20.5
52.5°	16.9
55°	14.8
57.5°	12.7
60°	11.3
62.5°	9.9
65°	8.5
67.5°	7.1
70°	5.6
72.5°	4.9
75°	4.2
77.5°	3.5
80°	2.8
82.5°	2.1
85°	1.4
87.5°	0.7



TEST NUMBER: P1287513

CATALOG NUMBER: P3AS17R359030D2WDE010 E3DLP1GPH

CANDELA DISTRIBUTION (continued):



(END OF REPORT)