

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1287550

Luminaire Tested: P3AS17R409030D2WDE010 E3DLP1WMH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1287550
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-21)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS17R409030D2WDE010 E3DLP1WMH
Description: 3in Adjustable Dim to Warm LED luminaire with, R40 optic, 3000K CCT AND, 90CRI ,
E3DLP1WMH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1057.9 lumens
Efficiency: N/A
Efficacy: 38.8 lumens/watt
Spacing Criteria (0/90/45): 0.73 / 0.73 / 0.74
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 27.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1287550

CATALOG NUMBER: P3AS17R409030D2WDE010 E3DLP1WMH

Luminous Intensity Polar Plot



TEST NUMBER: P1287550

CATALOG NUMBER: P3AS17R409030D2WDE010 E3DLP1WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	108	105	111	108	106	104	104	102	100		100	99	97		97
2	107	102	98	95	105	101	97	93	97	94	91		94	92	89		92
3	102	95	90	86	100	94	89	85	91	87	84		89	85	83		86
4	97	89	83	79	95	88	83	79	86	81	78		84	80	77		82
5	92	83	77	73	90	82	77	73	81	76	72		79	75	71		77
6	87	78	72	68	86	78	72	68	76	71	67		75	70	67		73
7	83	74	68	64	82	73	68	64	72	67	63		71	66	63		70
8	79	70	64	60	78	69	64	60	68	63	59		67	63	59		66
9	76	66	60	56	75	66	60	56	65	60	56		64	59	56		63
10	72	63	57	53	71	62	57	53	62	57	53		61	56	53		60

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	329447
5°	322759
10°	300529
15°	261931
20°	211092
25°	158211
30°	111232
35°	72866
40°	44111
45°	26359
50°	15727
55°	12654
60°	11359
65°	9703
70°	9232
75°	7286
80°	7324
85°	7296

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 26359 cd/sqm

TEST NUMBER: P1287550

CATALOG NUMBER: P3AS17R409030D2WDE010 E3DLP1WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	136.2	12.9
10°-20°	317.8	30.0
20°-30°	299.5	28.3
30°-40°	173.2	16.4
40°-50°	69.0	6.5
50°-60°	30.5	2.9
60°-70°	18.8	1.8
70°-80°	9.9	0.9
80°-90°	3.1	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	753.4	71.2
0°-40°	926.6	87.6
0°-60°	1026.1	97.0
0°-90°	1057.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1057.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1502	
5°	1466	136
15°	1154	318
25°	654	299
35°	272	173
45°	85	69
55°	33	31
65°	19	19
75°	9	10
85°	3	3
90°	0	

TEST NUMBER: P1287550

CATALOG NUMBER: P3AS17R409030D2WDE010 E3DLP1WMH

CANDELA DISTRIBUTION (FULL):

0°	
0°	1502.4
2.5°	1493.7
5°	1466.3
7.5°	1415.9
10°	1349.7
12.5°	1260.4
15°	1153.8
17.5°	1034.2
20°	904.6
22.5°	774.9
25°	653.9
27.5°	541.6
30°	439.3
32.5°	350.0
35°	272.2
37.5°	206.0
40°	154.1
42.5°	115.2
45°	85.0
47.5°	61.9
50°	46.1
52.5°	37.5
55°	33.1
57.5°	30.2
60°	25.9
62.5°	21.6
65°	18.7
67.5°	15.8
70°	14.4
72.5°	11.5
75°	8.6
77.5°	7.2
80°	5.8
82.5°	4.3
85°	2.9
87.5°	1.4
90°	0.0

(END OF REPORT)