

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1287558

Luminaire Tested: P3AS17R459030D2WDE010 E3DL1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1287558
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-27)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS17R459030D2WDE010 E3DL1GPH
Description: 3in Adjustable Dim to Warm LED luminaire with, R45 optic, 3000K CCT AND, 90CRI ,
E3DL1GPH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 789.0 lumens
Efficiency: N/A
Efficacy: 28.9 lumens/watt
Spacing Criteria (0/90/45): 0.69 / 0.69 / 0.69
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 27.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1287558

CATALOG NUMBER: P3AS17R459030D2WDE010 E3DL1GPH

Luminous Intensity Polar Plot



TEST NUMBER: P1287558

CATALOG NUMBER: P3AS17R459030D2WDE010 E3DL1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	114	111	109	107	111	109	107	105	105	103	102		101	100	99		98
2	109	104	100	97	106	102	99	96	99	96	94		96	94	92		93
3	104	98	93	89	102	96	92	88	94	90	87		91	88	86		89
4	99	92	87	83	97	91	86	82	89	85	81		87	83	80		85
5	94	87	81	77	93	86	81	77	84	80	76		82	79	76		81
6	90	82	77	73	89	81	76	72	80	75	72		78	74	71		77
7	86	78	72	68	85	77	72	68	76	71	68		75	71	67		74
8	83	74	68	65	82	73	68	64	72	68	64		71	67	64		70
9	79	70	65	61	78	70	65	61	69	64	61		68	64	61		67
10	76	67	62	58	75	67	62	58	66	61	58		65	61	58		65

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	296292
5°	289345
10°	265994
15°	225382
20°	174852
25°	122233
30°	76999
35°	45320
40°	25648
45°	12466
50°	4332
55°	3517
60°	3421
65°	3321
70°	3142
75°	2965
80°	2652
85°	1761

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 12466 cd/sqm

TEST NUMBER: P1287558

CATALOG NUMBER: P3AS17R459030D2WDE010 E3DL1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	121.7	15.4
10°-20°	272.6	34.6
20°-30°	231.5	29.3
30°-40°	110.4	14.0
40°-50°	33.3	4.2
50°-60°	8.5	1.1
60°-70°	6.3	0.8
70°-80°	3.7	0.5
80°-90°	1.0	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	625.8	79.3
0°-40°	736.2	93.3
0°-60°	777.9	98.6
0°-90°	789.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	789.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1351	
5°	1314	122
15°	993	273
25°	505	231
35°	169	110
45°	40	33
55°	9	8
65°	6	6
75°	4	4
85°	1	1
90°	0	

TEST NUMBER: P1287558

CATALOG NUMBER: P3AS17R459030D2WDE010 E3DL1GPH

CANDELA DISTRIBUTION (FULL):

0°	
0°	1351.2
2.5°	1342.8
5°	1314.5
7.5°	1265.8
10°	1194.6
12.5°	1100.0
15°	992.8
17.5°	873.5
20°	749.3
22.5°	623.0
25°	505.2
27.5°	398.0
30°	304.1
32.5°	228.6
35°	169.3
37.5°	124.9
40°	89.6
42.5°	62.1
45°	40.2
47.5°	22.6
50°	12.7
52.5°	9.9
55°	9.2
57.5°	8.5
60°	7.8
62.5°	7.1
65°	6.4
67.5°	5.6
70°	4.9
72.5°	4.2
75°	3.5
77.5°	2.8
80°	2.1
82.5°	1.4
85°	0.7
87.5°	0.7
90°	0.0

(END OF REPORT)