

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1287575

Luminaire Tested: P3AS17R459030D2WDE010 E3DLP1WMH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1287575
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-25)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS17R459030D2WDE010 E3DLP1WMH
Description: 3in Adjustable Dim to Warm LED luminaire with, R45 optic, 3000K CCT AND, 90CRI ,
E3DLP1WMH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1039.0 lumens
Efficiency: N/A
Efficacy: 38.1 lumens/watt
Spacing Criteria (0/90/45): 0.73 / 0.73 / 0.76
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 27.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1287575

CATALOG NUMBER: P3AS17R459030D2WDE010 E3DLP1WMH

Luminous Intensity Polar Plot



TEST NUMBER: P1287575

CATALOG NUMBER: P3AS17R459030D2WDE010 E3DLP1WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50			
RCR																						
0	119	119	119	119		116	116	116	116		111	111	111		106	106	106		102	102	102	100
1	113	110	107	105		111	108	106	103		104	102	100		100	99	97		97	96	94	93
2	107	102	98	94		105	100	96	93		97	94	91		94	91	89		91	89	87	86
3	102	95	90	85		100	93	89	85		91	87	83		88	85	82		86	83	81	79
4	96	88	83	78		94	87	82	78		85	81	77		83	79	76		81	78	75	74
5	91	83	77	72		90	82	76	72		80	75	71		78	74	71		77	73	70	69
6	87	78	72	67		85	77	71	67		75	70	66		74	69	66		73	69	66	64
7	83	73	67	63		81	72	67	63		71	66	62		70	65	62		69	65	61	60
8	79	69	63	59		77	68	63	59		67	62	58		66	62	58		65	61	58	56
9	75	65	59	55		74	65	59	55		64	59	55		63	58	55		62	58	55	53
10	72	62	56	52		71	61	56	52		61	55	52		60	55	52		59	55	52	50

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	309471
5°	302421
10°	278975
15°	242589
20°	199284
25°	155065
30°	114499
35°	80575
40°	50294
45°	27228
50°	14737
55°	12654
60°	11359
65°	9703
70°	8335
75°	8557
80°	7324
85°	7296

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 27228 cd/sqm

TEST NUMBER: P1287575

CATALOG NUMBER: P3AS17R459030D2WDE010 E3DLP1WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	127.2	12.2
10°-20°	295.4	28.4
20°-30°	293.3	28.2
30°-40°	188.9	18.2
40°-50°	72.7	7.0
50°-60°	29.6	2.8
60°-70°	18.7	1.8
70°-80°	10.1	1.0
80°-90°	3.1	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	715.9	68.9
0°-40°	904.8	87.1
0°-60°	1007.1	96.9
0°-90°	1039.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1039.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1411	
5°	1374	127
15°	1069	295
25°	641	293
35°	301	189
45°	88	73
55°	33	30
65°	19	19
75°	10	10
85°	3	3
90°	0	

TEST NUMBER: P1287575

CATALOG NUMBER: P3AS17R459030D2WDE010 E3DLP1WMH

CANDELA DISTRIBUTION (FULL):

0°	
0°	1411.3
2.5°	1404.1
5°	1373.9
7.5°	1322.0
10°	1252.9
12.5°	1166.5
15°	1068.6
17.5°	962.0
20°	854.0
22.5°	744.5
25°	640.9
27.5°	542.9
30°	452.2
32.5°	373.0
35°	301.0
37.5°	236.2
40°	175.7
42.5°	126.7
45°	87.8
47.5°	59.0
50°	43.2
52.5°	36.0
55°	33.1
57.5°	28.8
60°	25.9
62.5°	21.6
65°	18.7
67.5°	15.8
70°	13.0
72.5°	11.5
75°	10.1
77.5°	7.2
80°	5.8
82.5°	4.3
85°	2.9
87.5°	1.4
90°	0.0

(END OF REPORT)