

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1289583

Luminaire Tested: P3AS05R40W2N902765DE010 E3DL1GPH_6500K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1289583
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-23)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS05R40W2N902765DE010 E3DL1GPH_6500K
Description: 3in Adjustable Tunable White LED luminaire with, R40 optic, 6500K CCT AND, 90CRI ,
E3DL1GPH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 228.0 lumens
Efficiency: N/A
Efficacy: 38.7 lumens/watt
Spacing Criteria (0/90/45): 0.65 / 0.65 / 0.63
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 5.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1289583

CATALOG NUMBER: P3AS05R40W2N902765DE010 E3DL1GPH_6500K

Luminous Intensity Polar Plot





TEST NUMBER: P1289583

CATALOG NUMBER: P3AS05R40W2N902765DE010 E3DL1GPH_6500K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10		0			
RCR																										
0	119	119	119	119		116	116	116	116		111	111	111		106	106	106		102	102	102		100			
1	114	111	109	107		112	109	107	105		105	104	102		102	100	99		98	97	96		94			
2	109	105	101	98		107	103	100	97		100	97	95		97	95	93		94	92	91		89			
3	104	99	94	91		102	97	93	90		95	91	88		92	89	87		90	88	86		84			
4	100	93	88	85		98	92	88	84		90	86	83		88	85	82		86	84	81		80			
5	96	88	83	79		94	87	83	79		86	82	78		84	81	78		83	80	77		76			
6	92	84	79	75		91	83	78	75		82	77	74		81	77	74		79	76	73		72			
7	88	80	75	71		87	79	74	71		78	74	71		77	73	70		76	73	70		69			
8	85	76	71	68		84	76	71	67		75	70	67		74	70	67		73	69	67		65			
9	82	73	68	64		81	73	68	64		72	67	64		71	67	64		70	66	64		63			
10	78	70	65	62		78	70	65	61		69	64	61		68	64	61		67	64	61		60			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	100891
5°	97953
10°	88887
15°	73440
20°	52971
25°	32760
30°	17750
35°	9155
40°	4981
45°	2791
50°	1399
55°	1032
60°	965
65°	934
70°	898
75°	847
80°	758
85°	503

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 2791 cd/sqm

TEST NUMBER: P1289583

CATALOG NUMBER: P3AS05R40W2N902765DE010 E3DL1GPH_6500K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	41.0	18.0
10°-20°	88.1	38.6
20°-30°	62.9	27.6
30°-40°	23.1	10.1
40°-50°	7.3	3.2
50°-60°	2.5	1.1
60°-70°	1.8	0.8
70°-80°	1.1	0.5
80°-90°	0.3	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	192.0	84.2
0°-40°	215.1	94.3
0°-60°	224.9	98.6
0°-90°	228.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	228.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	460	
5°	445	41
15°	324	88
25°	135	63
35°	34	23
45°	9	7
55°	3	3
65°	2	2
75°	1	1
85°	0	0
90°	0	

TEST NUMBER: P1289583

CATALOG NUMBER: P3AS05R40W2N902765DE010 E3DL1GPH_6500K

CANDELA DISTRIBUTION (FULL):

0°	
0°	460.1
2.5°	456.6
5°	445.0
7.5°	425.8
10°	399.2
12.5°	365.4
15°	323.5
17.5°	276.5
20°	227.0
22.5°	178.3
25°	135.4
27.5°	99.4
30°	70.1
32.5°	49.1
35°	34.2
37.5°	24.3
40°	17.4
42.5°	12.5
45°	9.0
47.5°	6.1
50°	4.1
52.5°	2.9
55°	2.7
57.5°	2.5
60°	2.2
62.5°	2.0
65°	1.8
67.5°	1.6
70°	1.4
72.5°	1.2
75°	1.0
77.5°	0.8
80°	0.6
82.5°	0.4
85°	0.2
87.5°	0.2
90°	0.0

(END OF REPORT)