

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1289608

Luminaire Tested: P3AS05R40W2N902765DE010 E3DL1WMH\_2700K

Issue Date: 1/30/2026

**Test Information**

Test Method: LM-79-2019  
Report Number: P1289608  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-23)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS05R40W2N902765DE010 E3DL1WMH\_2700K  
Description: 3in Adjustable Tunable White LED luminaire with, R40 optic, 2700K CCT AND, 90CRI ,  
E3DL1WMH TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 418.0 lumens  
Efficiency: N/A  
Efficacy: 70.9 lumens/watt  
Spacing Criteria (0/90/45): 0.65 / 0.65 / 0.63  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct

Input Watts (W): 5.9  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1289608

CATALOG NUMBER: P3AS05R40W2N902765DE010 E3DL1WMH\_2700K

### Luminous Intensity Polar Plot





TEST NUMBER: P1289608

CATALOG NUMBER: P3AS05R40W2N902765DE010 E3DL1WMH\_2700K

### COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

|     |     |     |     |     |  |     |     |     |     |  |     |     |     |  |     |     |     |  |     |     |     |  |     |  |  |   |
|-----|-----|-----|-----|-----|--|-----|-----|-----|-----|--|-----|-----|-----|--|-----|-----|-----|--|-----|-----|-----|--|-----|--|--|---|
| RF  | 20  |     |     |     |  | 20  |     |     |     |  | 20  |     |     |  |     | 20  |     |  |     |     | 20  |  |     |  |  |   |
| RC  | 80  |     |     |     |  | 70  |     |     |     |  | 50  |     |     |  |     | 30  |     |  |     |     | 10  |  |     |  |  | 0 |
| RW  | 70  | 50  | 30  | 10  |  | 70  | 50  | 30  | 10  |  | 50  | 30  | 10  |  | 50  | 30  | 10  |  | 50  | 30  | 10  |  | 0   |  |  |   |
| RCR |     |     |     |     |  |     |     |     |     |  |     |     |     |  |     |     |     |  |     |     |     |  |     |  |  |   |
| 0   | 119 | 119 | 119 | 119 |  | 116 | 116 | 116 | 116 |  | 111 | 111 | 111 |  | 106 | 106 | 106 |  | 102 | 102 | 102 |  | 100 |  |  |   |
| 1   | 114 | 111 | 109 | 107 |  | 112 | 109 | 107 | 105 |  | 105 | 104 | 102 |  | 102 | 100 | 99  |  | 98  | 97  | 96  |  | 94  |  |  |   |
| 2   | 109 | 105 | 101 | 98  |  | 107 | 103 | 100 | 97  |  | 100 | 97  | 95  |  | 97  | 95  | 93  |  | 94  | 92  | 91  |  | 89  |  |  |   |
| 3   | 104 | 99  | 94  | 91  |  | 102 | 97  | 93  | 90  |  | 95  | 91  | 88  |  | 92  | 89  | 87  |  | 90  | 88  | 86  |  | 84  |  |  |   |
| 4   | 100 | 93  | 88  | 85  |  | 98  | 92  | 88  | 84  |  | 90  | 86  | 83  |  | 88  | 85  | 82  |  | 86  | 84  | 81  |  | 80  |  |  |   |
| 5   | 96  | 88  | 83  | 79  |  | 94  | 88  | 83  | 79  |  | 86  | 82  | 78  |  | 84  | 81  | 78  |  | 83  | 80  | 77  |  | 76  |  |  |   |
| 6   | 92  | 84  | 79  | 75  |  | 91  | 83  | 78  | 75  |  | 82  | 78  | 74  |  | 81  | 77  | 74  |  | 79  | 76  | 73  |  | 72  |  |  |   |
| 7   | 88  | 80  | 75  | 71  |  | 87  | 79  | 74  | 71  |  | 78  | 74  | 71  |  | 77  | 73  | 70  |  | 76  | 73  | 70  |  | 69  |  |  |   |
| 8   | 85  | 76  | 71  | 68  |  | 84  | 76  | 71  | 67  |  | 75  | 70  | 67  |  | 74  | 70  | 67  |  | 73  | 69  | 67  |  | 65  |  |  |   |
| 9   | 82  | 73  | 68  | 64  |  | 81  | 73  | 68  | 64  |  | 72  | 67  | 64  |  | 71  | 67  | 64  |  | 70  | 66  | 64  |  | 63  |  |  |   |
| 10  | 78  | 70  | 65  | 62  |  | 78  | 70  | 65  | 61  |  | 69  | 64  | 61  |  | 68  | 64  | 61  |  | 67  | 64  | 61  |  | 60  |  |  |   |

**AVERAGE LUMINANCE (cd/sqm):**

|     | 0°     |
|-----|--------|
| 0°  | 184963 |
| 5°  | 179595 |
| 10° | 162967 |
| 15° | 134643 |
| 20° | 97122  |
| 25° | 60076  |
| 30° | 32511  |
| 35° | 16811  |
| 40° | 9131   |
| 45° | 5117   |
| 50° | 2559   |
| 55° | 1912   |
| 60° | 1710   |
| 65° | 1660   |
| 70° | 1603   |
| 75° | 1525   |
| 80° | 1389   |
| 85° | 1006   |

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°

Vertical Angle:  $45^\circ$

Luminance: 5117 cd/sqm

TEST NUMBER: P1289608

CATALOG NUMBER: P3AS05R40W2N902765DE010 E3DL1WMH\_2700K

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 75.2   | 18.0      |
| 10°-20°   | 161.5  | 38.6      |
| 20°-30°   | 115.2  | 27.6      |
| 30°-40°   | 42.4   | 10.2      |
| 40°-50°   | 13.4   | 3.2       |
| 50°-60°   | 4.6    | 1.1       |
| 60°-70°   | 3.2    | 0.8       |
| 70°-80°   | 1.9    | 0.5       |
| 80°-90°   | 0.6    | 0.1       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| 0°-30°    | 351.9  | 84.2      |
| 0°-40°    | 394.4  | 94.3      |
| 0°-60°    | 412.4  | 98.6      |
| 0°-90°    | 418.0  | 100.0     |
| 90°-120°  | 0.0    | 0.0       |
| 90°-150°  | 0.0    | 0.0       |
| 90°-180°  | 0.0    | 0.0       |
| 0°-180°   | 418.0  | 100.0     |

**CANDELA DISTRIBUTION:**

|     | 0°  | Flux |
|-----|-----|------|
| 0°  | 844 |      |
| 5°  | 816 | 75   |
| 15° | 593 | 161  |
| 25° | 248 | 115  |
| 35° | 63  | 42   |
| 45° | 16  | 13   |
| 55° | 5   | 5    |
| 65° | 3   | 3    |
| 75° | 2   | 2    |
| 85° | 0   | 1    |
| 90° | 0   |      |

TEST NUMBER: P1289608

CATALOG NUMBER: P3AS05R40W2N902765DE010 E3DL1WMH\_2700K

**CANDELA DISTRIBUTION (FULL):**

|       | 0°    |
|-------|-------|
| 0°    | 843.5 |
| 2.5°  | 837.0 |
| 5°    | 815.9 |
| 7.5°  | 780.7 |
| 10°   | 731.9 |
| 12.5° | 669.8 |
| 15°   | 593.1 |
| 17.5° | 507.0 |
| 20°   | 416.2 |
| 22.5° | 326.8 |
| 25°   | 248.3 |
| 27.5° | 182.3 |
| 30°   | 128.4 |
| 32.5° | 90.1  |
| 35°   | 62.8  |
| 37.5° | 44.5  |
| 40°   | 31.9  |
| 42.5° | 23.0  |
| 45°   | 16.5  |
| 47.5° | 11.1  |
| 50°   | 7.5   |
| 52.5° | 5.4   |
| 55°   | 5.0   |
| 57.5° | 4.7   |
| 60°   | 3.9   |
| 62.5° | 3.6   |
| 65°   | 3.2   |
| 67.5° | 2.9   |
| 70°   | 2.5   |
| 72.5° | 2.2   |
| 75°   | 1.8   |
| 77.5° | 1.4   |
| 80°   | 1.1   |
| 82.5° | 0.7   |
| 85°   | 0.4   |
| 87.5° | 0.4   |
| 90°   | 0.0   |

(END OF REPORT)