

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1289609

Luminaire Tested: P3AS05R40W2N902765DE010 E3DL1WMH_3000K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1289609
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-23)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS05R40W2N902765DE010 E3DL1WMH_3000K
Description: 3in Adjustable Tunable White LED luminaire with, R40 optic, 3000K CCT AND, 90CRI ,
E3DL1WMH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 461.0 lumens
Efficiency: N/A
Efficacy: 78.1 lumens/watt
Spacing Criteria (0/90/45): 0.65 / 0.65 / 0.63
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 5.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1289609
CATALOG NUMBER: P3AS05R40W2N902765DE010 E3DL1WMH_3000K

Luminous Intensity Polar Plot





TEST NUMBER: P1289609
 CATALOG NUMBER: P3AS05R40W2N902765DE010 E3DL1WMH_3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20		
RC	80				70				50				30				10		0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10		0
RCR																			
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102		100
1	114	111	109	107	112	109	107	105	105	104	102	102	100	99	98	97	96		94
2	109	105	101	98	107	103	100	97	100	97	95	97	95	93	94	92	91		89
3	104	99	94	91	102	97	93	90	95	91	88	92	89	87	90	88	86		84
4	100	93	88	85	98	92	88	84	90	86	83	88	85	82	86	84	81		80
5	96	88	83	79	94	87	83	79	86	82	78	84	81	78	83	80	77		76
6	92	84	79	75	91	83	78	75	82	77	74	81	77	74	79	76	73		72
7	88	80	75	71	87	79	74	71	78	74	71	77	73	70	76	73	70		69
8	85	76	71	68	84	76	71	67	75	70	67	74	70	67	73	69	67		65
9	82	73	68	64	81	73	68	64	72	67	64	71	67	64	70	66	64		63
10	78	70	65	62	78	70	65	61	69	64	61	68	64	61	67	64	61		60

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	203997
5°	198062
10°	179734
15°	148491
20°	107109
25°	66246
30°	35879
35°	18524
40°	10076
45°	5644
50°	2831
55°	2103
60°	1930
65°	1868
70°	1795
75°	1694
80°	1515
85°	1006

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 5644 cd/sqm



TEST NUMBER: P1289609

CATALOG NUMBER: P3AS05R40W2N902765DE010 E3DL1WMH_3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	82.9	18.0
10°-20°	178.1	38.6
20°-30°	127.1	27.6
30°-40°	46.8	10.1
40°-50°	14.7	3.2
50°-60°	5.1	1.1
60°-70°	3.6	0.8
70°-80°	2.1	0.5
80°-90°	0.6	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	388.2	84.2
0°-40°	434.9	94.3
0°-60°	454.8	98.6
0°-90°	461.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	461.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	930	
5°	900	83
15°	654	178
25°	274	127
35°	69	47
45°	18	15
55°	6	5
65°	4	4
75°	2	2
85°	0	1
90°	0	



TEST NUMBER: P1289609
CATALOG NUMBER: P3AS05R40W2N902765DE010 E3DL1WMH_3000K

CANDELA DISTRIBUTION (FULL):

	0°
0°	930.3
2.5°	923.1
5°	899.8
7.5°	861.0
10°	807.2
12.5°	738.8
15°	654.1
17.5°	559.1
20°	459.0
22.5°	360.5
25°	273.8
27.5°	201.0
30°	141.7
32.5°	99.3
35°	69.2
37.5°	49.1
40°	35.2
42.5°	25.3
45°	18.2
47.5°	12.3
50°	8.3
52.5°	5.9
55°	5.5
57.5°	5.1
60°	4.4
62.5°	4.0
65°	3.6
67.5°	3.2
70°	2.8
72.5°	2.4
75°	2.0
77.5°	1.6
80°	1.2
82.5°	0.8
85°	0.4
87.5°	0.4
90°	0.0

(END OF REPORT)