

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1287615

Luminaire Tested: P3AS17R559030D2WDE010 E3D1WMH

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1287615
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2501-338-14)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS17R559030D2WDE010 E3D1WMH
Description: 3in Adjustable Dim to Warm LED luminaire with, R55 optic, 3000K CCT AND, 90CRI , E3D1WM TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1858.0 lumens
Efficiency: N/A
Efficacy: 68.1 lumens/watt
Spacing Criteria (0/90/45): 0.93 / 0.93 / 0.82
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 27.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1287615

CATALOG NUMBER: P3AS17R559030D2WDE010 E3D1WMH

Luminous Intensity Polar Plot



TEST NUMBER: P1287615

CATALOG NUMBER: P3AS17R559030D2WDE010 E3D1WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	114	111	109	107	112	109	107	105	105	104	102		102	100	99		98
2	109	105	101	98	107	103	100	97	100	97	95		97	95	93		94
3	104	98	94	90	102	97	93	90	95	91	88		92	89	87		90
4	100	93	88	84	98	92	87	84	90	86	83		88	84	82		86
5	95	88	83	79	94	87	82	78	85	81	78		84	80	77		82
6	91	83	78	74	90	82	77	74	81	76	73		80	76	73		78
7	87	79	73	70	86	78	73	69	77	72	69		76	72	69		75
8	83	75	69	66	82	74	69	66	73	69	65		72	68	65		71
9	80	71	66	62	79	71	66	62	70	65	62		69	65	62		68
10	77	68	62	59	76	67	62	59	67	62	59		66	62	59		65

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	538795
5°	519721
10°	538311
15°	530718
20°	491186
25°	397233
30°	238062
35°	80682
40°	22213
45°	9861
50°	2900
55°	535
60°	307
65°	363
70°	449
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 9861 cd/sqm

TEST NUMBER: P1287615

CATALOG NUMBER: P3AS17R559030D2WDE010 E3D1WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	228.4	12.3
10°-20°	650.9	35.0
20°-30°	723.5	38.9
30°-40°	225.2	12.1
40°-50°	27.1	1.5
50°-60°	2.1	0.1
60°-70°	0.7	0.0
70°-80°	0.1	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1602.9	86.3
0°-40°	1828.1	98.4
0°-60°	1857.2	100.0
0°-90°	1858.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1858.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2457	
5°	2361	228
15°	2338	651
25°	1642	724
35°	301	225
45°	32	27
55°	1	2
65°	1	1
75°	0	0
85°	0	0
90°	0	

TEST NUMBER: P1287615

CATALOG NUMBER: P3AS17R559030D2WDE010 E3D1WMH

CANDELA DISTRIBUTION (FULL):

0°	
0°	2457.1
1°	2447.9
2°	2423.9
3°	2394.3
4°	2367.5
5°	2361.1
6°	2368.2
7°	2383.0
8°	2399.9
9°	2413.4
10°	2417.6
11°	2414.8
12°	2403.5
13°	2385.8
14°	2365.4
15°	2337.8
16°	2306.1
17°	2265.8
18°	2220.7
19°	2166.3
20°	2104.9
21°	2035.0
22°	1952.4
23°	1861.4
24°	1756.9
25°	1641.8
26°	1515.5
27°	1381.4
28°	1238.1
29°	1090.6
30°	940.2
31°	789.2
32°	641.6
32.5°	576.0
33°	508.2
34°	393.2
35°	301.4
36°	229.4
37°	170.1
37.5°	145.4
38°	126.4
39°	96.0
40°	77.6
42.5°	49.4
45°	31.8



TEST NUMBER: P1287615

CATALOG NUMBER: P3AS17R559030D2WDE010 E3D1WMH

CANDELA DISTRIBUTION (continued):

	0°
47.5°	19.1
50°	8.5
52.5°	2.8
55°	1.4
57.5°	0.7
60°	0.7
62.5°	0.7
65°	0.7
67.5°	0.7
70°	0.7
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)