

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1287622

Luminaire Tested: P3AS17R559030D2WDE010 E3DLD1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1287622
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-34)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS17R559030D2WDE010 E3DLD1GPH
Description: 3in Adjustable Dim to Warm LED luminaire with, R55 optic, 3000K CCT AND, 90CRI ,
E3DLD1GPH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 597.0 lumens
Efficiency: N/A
Efficacy: 21.9 lumens/watt
Spacing Criteria (0/90/45): 0.91 / 0.91 / 0.97
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 27.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1287622
CATALOG NUMBER: P3AS17R559030D2WDE010 E3DLD1GPH

Luminous Intensity Polar Plot





TEST NUMBER: P1287622
 CATALOG NUMBER: P3AS17R559030D2WDE010 E3DLD1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	112	109	106	103	110	107	104	102	103	100	98	99	97	95	95	94	93	91			
2	105	100	95	91	103	98	93	90	94	91	88	91	88	86	89	86	84	82			
3	99	91	85	81	97	90	84	80	87	82	79	85	81	77	82	79	76	74			
4	93	84	77	72	91	83	77	72	80	75	71	78	74	70	76	73	69	68			
5	87	77	71	66	85	76	70	65	75	69	65	73	68	64	71	67	64	62			
6	82	72	65	60	80	71	64	60	69	64	59	68	63	59	66	62	58	57			
7	77	67	60	55	76	66	59	55	65	59	54	63	58	54	62	57	54	52			
8	73	62	55	51	72	62	55	51	60	55	50	59	54	50	58	53	50	48			
9	69	58	51	47	68	58	51	47	57	51	47	56	50	46	55	50	46	45			
10	65	55	48	44	64	54	48	44	53	47	43	52	47	43	52	47	43	42			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	112250
5°	110808
10°	106455
15°	99569
20°	90821
25°	81029
30°	70872
35°	58892
40°	46430
45°	31476
50°	19240
55°	9978
60°	9298
65°	8769
70°	8142
75°	7202
80°	7072
85°	5284

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 31476 cd/sqm



TEST NUMBER: P1287622

CATALOG NUMBER: P3AS17R559030D2WDE010 E3DLD1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	47.2	7.9
10°-20°	122.6	20.5
20°-30°	153.5	25.7
30°-40°	137.0	23.0
40°-50°	80.2	13.4
50°-60°	27.7	4.6
60°-70°	16.7	2.8
70°-80°	9.3	1.6
80°-90°	2.7	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	323.3	54.2
0°-40°	460.3	77.1
0°-60°	568.3	95.2
0°-90°	597.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	597.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	512	
5°	503	47
15°	439	123
25°	335	153
35°	220	137
45°	102	80
55°	26	28
65°	17	17
75°	8	9
85°	2	3
90°	0	



TEST NUMBER: P1287622

CATALOG NUMBER: P3AS17R559030D2WDE010 E3DLD1GPH

CANDELA DISTRIBUTION (FULL):

	0°
0°	511.9
2.5°	509.1
5°	503.4
7.5°	492.2
10°	478.1
12.5°	460.4
15°	438.6
17.5°	415.3
20°	389.2
22.5°	362.4
25°	334.9
27.5°	307.4
30°	279.9
32.5°	250.3
35°	220.0
37.5°	190.4
40°	162.2
42.5°	131.9
45°	101.5
47.5°	77.6
50°	56.4
52.5°	36.7
55°	26.1
57.5°	23.3
60°	21.2
62.5°	19.0
65°	16.9
67.5°	14.8
70°	12.7
72.5°	10.6
75°	8.5
77.5°	7.1
80°	5.6
82.5°	3.5
85°	2.1
87.5°	1.4
90°	0.0

(END OF REPORT)