

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1289652

Luminaire Tested: P3AS05R40W2N902765DE010 E3DLP1GPH_3500K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1289652
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-21)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS05R40W2N902765DE010 E3DLP1GPH_3500K
Description: 3in Adjustable Tunable White LED luminaire with, R40 optic, 3500K CCT AND, 90CRI ,
E3DLP1GPH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 145.0 lumens
Efficiency: N/A
Efficacy: 24.6 lumens/watt
Spacing Criteria (0/90/45): 0.73 / 0.73 / 0.74
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 5.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1289652

CATALOG NUMBER: P3AS05R40W2N902765DE010 E3DLP1GPH_3500K

Luminous Intensity Polar Plot



TEST NUMBER: P1289652

CATALOG NUMBER: P3AS05R40W2N902765DE010 E3DLP1GPH_3500K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	113	110	108	105	111	108	106	104	104	102	100	100	99	97	97	96	95	93		
2	107	102	98	95	105	101	97	93	97	94	91	94	92	89	92	89	88	86		
3	102	95	90	86	100	94	89	85	91	87	84	89	85	83	86	84	81	80		
4	97	89	83	79	95	88	83	79	86	81	78	84	80	77	82	78	76	74		
5	92	83	77	73	90	82	77	73	81	76	72	79	75	71	77	74	71	69		
6	87	78	72	68	86	78	72	68	76	71	67	75	70	67	73	69	66	65		
7	83	74	68	64	82	73	68	63	72	67	63	71	66	63	70	66	62	61		
8	79	70	64	60	78	69	64	60	68	63	59	67	63	59	66	62	59	58		
9	76	66	60	56	75	66	60	56	65	60	56	64	59	56	63	59	56	54		
10	72	63	57	53	71	62	57	53	62	57	53	61	56	53	60	56	53	51		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	45150
5°	44244
10°	41193
15°	35891
20°	28936
25°	21679
30°	15243
35°	9985
40°	6040
45°	3597
50°	2149
55°	1720
60°	1579
65°	1349
70°	1282
75°	1017
80°	1010
85°	1006

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 3597 cd/sqm

TEST NUMBER: P1289652

CATALOG NUMBER: P3AS05R40W2N902765DE010 E3DLP1GPH_3500K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	18.7	12.9
10°-20°	43.5	30.0
20°-30°	41.0	28.3
30°-40°	23.7	16.4
40°-50°	9.4	6.5
50°-60°	4.2	2.9
60°-70°	2.6	1.8
70°-80°	1.4	0.9
80°-90°	0.4	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	103.2	71.2
0°-40°	127.0	87.6
0°-60°	140.6	96.9
0°-90°	145.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	145.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	206	
5°	201	19
15°	158	44
25°	90	41
35°	37	24
45°	12	9
55°	4	4
65°	3	3
75°	1	1
85°	0	0
90°	0	

TEST NUMBER: P1289652

CATALOG NUMBER: P3AS05R40W2N902765DE010 E3DLP1GPH_3500K

CANDELA DISTRIBUTION (FULL):

0°	
0°	205.9
2.5°	204.7
5°	201.0
7.5°	194.1
10°	185.0
12.5°	172.7
15°	158.1
17.5°	141.7
20°	124.0
22.5°	106.2
25°	89.6
27.5°	74.2
30°	60.2
32.5°	48.0
35°	37.3
37.5°	28.2
40°	21.1
42.5°	15.8
45°	11.6
47.5°	8.5
50°	6.3
52.5°	5.1
55°	4.5
57.5°	4.1
60°	3.6
62.5°	3.0
65°	2.6
67.5°	2.2
70°	2.0
72.5°	1.6
75°	1.2
77.5°	1.0
80°	0.8
82.5°	0.6
85°	0.4
87.5°	0.2
90°	0.0

(END OF REPORT)